

PANDUIT® PANACEA™ LS7 Thermal Transfer Printer and Cassettes

pan•a•cea\pān'ə-sē'ə\ n: a solution to all problems.

The PANACEA LS7 Hand-Held Thermal Transfer printer is the solution for your network labeling. This printer is designed for fast and easy TIA/EIA-606-A compliant labeling.


- Professional:** High quality labels that stay where you put them and will not smear
- Powerful:** Mark patch panels, faceplates, components and cables with precision
- Easy:** Fast loading cassettes and simple operation
- Cost Effective:** Affordable and feature abundant. Case and batteries are included



Key Features

Benefits

Label cassette includes both label material and ribbon	Makes changing labels fast and easy
Firmware designed specifically to meet communication market needs	Minimizes waste and allows for effortless patch panel, faceplate and cable marking
Advanced programming allows you to specify legend spacing	No more guessing how many spaces are needed to line up your legends with ports
Label materials developed for use on textured and curved surfaces	Ensures patch panel, faceplate and cable labels stay where you put them
Laminated materials available	Provide abrasion, chemical and UV resistance
Repeat legend function	Eliminates repetitive typing for marking cables
Advanced alpha and numeric serialization	Speeds label creation
Store up to 9 label files	Saves time by recalling frequently used labels
Automatic font sizing	Eliminates guesswork in label design
Symbol library	Includes commonly used communication symbols
Vertical and horizontal lines	Separate legends on patch panel, faceplate and 110 block labels improve clarity
Affordable price	Easy on your budget without sacrificing features



Cable Labeling



Patch Panel Labeling



Outlet Labeling



Pathway Labeling

PANDUIT® PANACEA™ LS7 Thermal Transfer Printer and Cassettes

Ordering Information

Printer and Accessories

Part Number	Part Description	Std. Pkg. Qty.*	Std. Ctn. Qty.
LS7	Printer Kit (includes printer, 3/4" (18mm) non-laminated black/white cassette, hardside carrying case, wrist strap, 6 AA alkaline batteries, label separator tool and operator's manual)	1	4
LS7-ACS	120 VAC adapter**	1	6
LS7-CLN	Cleaning cassette	1	20



Component Cassettes for PANACEA LS7 Thermal Transfer Printer (for flat label applications only)

Part Number	Part Description	Height		Length		Std. Pkg. Qty.*	Std. Ctn. Qty.
		in.	mm.	ft.	m		
LS7-25-1	Black/white laminated polyester label cassette	.236	6.0	26.2	8.0	1	20
LS7-25-2	Black/clear laminated polyester label cassette						
LS7-38-1	Black/white laminated polyester label cassette	.354	9.0	26.2	8.0	1	20
LS7-38-2	Black/clear laminated polyester label cassette						
LS7-50-1	Black/white laminated polyester label cassette	.472	12.0	26.2	8.0	1	20
LS7-50-2	Black/clear laminated polyester label cassette						
LS7-75-4	Black/yellow laminated polyester label cassette	.708	18.0	26.2	8.0	1	20
LS7-75-5	Black/orange laminated polyester label cassette						
LS7-75-6	Black/red laminated polyester label cassette						
LS7-75NL-1	Black/white non-laminated polyester label cassette						

Cable Marking Cassettes for PANACEA LS7 Thermal Transfer Printer

Part Number	Part Description	Height		Length		Std. Pkg. Qty.*	Std. Ctn. Qty.
		in.	mm.	ft.	m		
LS7-75NL-1	Black/white non-laminated polyester label cassette	.708	18.0	26.2	8.0	1	20
LS7-75NL-2	Black/clear non-laminated polyester label cassette						

ULTIMATE ID™† Non-Laminated Label Cassette

Part Number	Part Description	Height		Length		Std. Pkg. Qty.*	Std. Ctn. Qty.
		in.	mm.	ft.	m		
UJLS7BW	Black/white non-laminated polyester label cassette	.236	6.0	26.2	8.0	1	20

For non-adhesive applications, do not remove liner from label.

* Order number required.

** Cannot be used to recharge batteries

†For detailed information on the ULTIMATE ID Network Labeling System, request product bulletin SA-IDCB01.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
Phone: 800-777-3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44 208-601-7200

PANDUIT ASIA PACIFIC PTE. LTD.
Republic of Singapore
Phone: (65) 6379 6700

PANDUIT JAPAN
Tokyo, Japan
Phone: (81) (3) 3767-7011

PANDUIT LATIN AMERICA
Jalisco, Mexico
Phone: (52) (333) 666-2501

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: (61) 3-9794 9020

For a copy of PANDUIT product warranties, log on to www.panduit.com/warranty



For more information or to request a catalog

800-777-3300

cs@panduit.com

www.panduit.com

Copyright © PANDUIT Corp. All rights reserved.
Printed in U.S.A.

SA-IDCB12

11/2003

replaces SA-IDCB1000A