

QuickNet™ Plug Pack Housings

QuickNet™ Plug Pack Housings facilitate quick and easy connection and removal of patch cords from a variety of switches, reducing the time and cost associated with installing and maintaining structured cabling links. Innovative design features of the plug pack allow multiple patch cords to be installed simultaneously with one hand for speed of deployment. Modular plugs are extended forward, eliminating interference with the front bezels of many switches. Individual cable links can be removed without disrupting service to the other network connections. QuickNet™ Plug Pack Housings accept all Panduit® UTP, and shielded Category 6A/6 copper patch cords.



Key Features

Benefits

Compatible with most RJ45 48-port, 1 RU switch blades and chassis including Cisco* Catalyst and Nexus series switches	Utilizes precision geometry for quick connection to the switch; standard, QPPN version compatible with Cisco* Catalyst 6K, 4K, and now 3750 and 3560 series switches; QPPNR recessed version compatible with Cisco* Nexus 7K series switches.
Integrated finger latch	Enables quick, one-handed installation and removal of QuickNet™ Plug Pack Assemblies from the switch
Variety of configurations	Available in six, eight, or twelve cable assemblies for optimal switch compatibility
Modular design	Snaps modular plugs directly into switches and utilizes an integral release tab to ensure easy on-site moves, adds, and changes
Low profile design	Allows plug pack assemblies to be installed side by side or stacked on top of each other providing maximum port density in high density installations
Marker ties (optional)	Enables easy identification in high density installations; provides additional level of security when combined with optional lock-in device
Removal tool (optional)	Allows individual patch cords to be removed without disrupting other network connections
Lock-in device (optional)	Prevents unauthorized removal of patch cords from the switch for an additional level of security

Application Information

Switch blades periodically need to be replaced or exchanged due to system upgrades or repair/replacement. Due to high port density, removing and re-connecting each individual patch cord is time consuming. Each QuickNet™ Plug Pack Housing accepts six, eight or twelve Panduit patch cords, allowing them to be installed, disconnected, and re-connected quicker than traditional methods, resulting in a 67% improvement of mean time to repair.



Optional lock-in device and marker ties provide an additional level of network security.



Optional labels allow each assembly and port to be identified per TIA-606-A labeling standard.

*Cisco is a registered trademark of Cisco Technology, Inc.

QuickNet™ Plug Pack Housings

Ordering Information

Part Number	Description	Std. Pkg. Qty.	Std. Ctn. Qty.
QuickNet™ Plug Pack Housings			
QPPN6++	QuickNet™ Plug Pack Individual Housing accepts six Panduit RJ45 patch cords.	1	10
QPPN8++	QuickNet™ Plug Pack Individual Housing accepts eight Panduit RJ45 patch cords.	1	10
QPPN12++	QuickNet™ Plug Pack Individual Housing accepts twelve Panduit RJ45 patch cords.	1	10
Recessed QuickNet™ Plug Pack Housings			
QPPNR6S	QuickNet™ Plug Pack Individual Recessed Housing accepts six Panduit RJ45 patch cords. Compatible with Cisco Nexus 7000 Series Switch.	1	10
Accessories			
QPPRT	Removal tool allows individual patch cords to be removed without disruption of other network connections.	1	10
QPPLD6-X	Lock-in device prevents unauthorized removal of patch cords from the 6 and 12 plug pack assembly. (Recommended installed quantity two per 6-pack, four per 12-pack).	10	100
QPPLD8-X	Lock-in device prevents unauthorized removal of patch cords from the 8 plug pack assembly. (Recommended installed quantity two per 8-pack).	10	100

Order in multiples of Standard Package Quantity.
 ++ Available in BU (Blue), BL (Black), RD (Red) or WH (White).
 Recessed version, part number QPPNR6S, is silver.

Plug Pack Compatibility

Cisco Switch Series	Type	Part Number
Catalyst 6000	6-Pack and 12-Pack	QPPN6** QPPN12**
Catalyst 4000	8-Pack	QPPN8**
Catalyst 7000	6-Pack	QPPNR6S
Catalyst 3750, 3560, 2960	6-Pack	QPPN6**



6-Pack Plug Pack – QPPN6BU



12-Pack Plug Pack – QPPN12BU




6-Pack recessed Plug Pack – QPPR6S



QuickNet™ Removal Tool – QPPRT



QuickNet™ Lock-In Device – QPPLD6-X and QPPLD8-X



Copper Patch Cords are available in a variety of lengths and colors for UTP and Shielded Category 6A, 6, and UTP Category 5e installations

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
 Markham, Ontario
 cs-cdn@panduit.com
 Phone: 800.777.3300

PANDUIT EUROPE LTD.
 London, UK
 cs-emea@panduit.com
 Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
 Republic of Singapore
 cs-ap@panduit.com
 Phone: 65.6305.7575

PANDUIT JAPAN
 Tokyo, Japan
 cs-japan@panduit.com
 Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
 Guadalajara, Mexico
 cs-la@panduit.com
 Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
 Victoria, Australia
 cs-aus@panduit.com
 Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
 or by phone: 800.777.3300 and reference COCB24



©2012 Panduit Corp.
 ALL RIGHTS RESERVED.
 Product Bulletin Number **WW-COCB24**
 3/2012