



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART#	DESCRIPTION	WEIGHT*
CJ5E88TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE. RED WIRE CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.53 LB/100 PCS (695g/100 PCS)


*WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX



- NOTES:
1. RED WIRE CAP DESIGNATES CATEGORY 5e PERFORMANCE.
 2. TO DESIGNATE A JACK COLOR, ADD A TWO LETTER COLOR SUFFIX. SEE CURRENT CATALOG FOR AVAILABLE PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
 3. MATERIAL:
MODULE HOUSING - ABS
WIRE CAP - PC
STRAIN RELIEF CLIP - PC
 4. ALL TX5e CAT5e 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
 5. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ACTUAL SIZE



PART NUMBER	CJ5E88TG**	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A

TITLE	TX5e CAT5e JACK MODULE		
	CUSTOMER DRAWING		
ITEM REVISION NAME	M02043CB/05		

DATASET FILE NAME	M02043CB_DC05/05A	PANDUIT
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		

.x ± .1 [2.54]		.xxx ± .005 [.127]	DRAWING NUMBER: 02043-05
.xx ± .01 [.25]		ANGLES ± 5 °	
THIRD ANGLE PROJECTION			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	12-9-13	BJN	EJH	EJH	UPDATED	02043-05
R	8-31-05	MDJr	PBC	PBC	RELEASED TO PRODUCTION	02043-05

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							MDJr	8-31-05	PBC	FULL		A

D101000DA/14