

Panduit Patch Cord Guide

Cisco Nexus^ Switches	RU	Downlink Ports	Port Type	Copper Patch Cord	Copper Breakout	2-Fiber Patch Cord	Fiber Breakout	Uplink Ports	Port Type	Copper Assembly	12-Fiber Assembly
N9K-C9372PX-E	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C9396PX	2	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6 or 12	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C9372TX-E	1	48	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C93120TX	2	96	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C93108TC-EX	1	48	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+/QSFP28	PQSFP***MBU	FZTRL7N7NANM***
N9K-C9396TX	2	48	RJ45	UTP28X*BU	NA	NA	NA	6 or 12	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C93128TX	3	96	RJ45	UTP28X*BU	NA	NA	NA	6 or 8	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C93180YC-EX	1	48	SFP+/SFP28	PSF*PX**MBU	NA	FZ2ERLNLNSNM***	NA	6	QSFP+/QSFP28	PQSFP***MBU	FZTRL7N7NANM***
N9K-C92160YC-X	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6 or 4	QSFP+/QSFP28	PQSFP***MBU	FZTRL7N7NANM***
N9K-C9272Q	2	72	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N9K-C9336PQ	2	32	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N9K-C9332PQ	1	26	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-92304QC	2	56	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	8	QSFP28	PQSFP2**MBU	FZTRL7N7NANM***
N9K-C9236C	1	32	QSFP+/QSFP28	PQSFP***MBU	PHQ4SFP***MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N9K-C9372PX-E-B18Q	2	96	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	12	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C9372TX-E-B18Q	2	96	RJ45	UTP28X*BU	NA	NA	NA	12	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C9396TX-B18Q	4	96	RJ45	UTP28X*BU	NA	NA	NA	12	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C9396PX-B18Q	4	96	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	24	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N9K-C93120TX-B18Q	6	192	RJ45	UTP28X*BU	NA	NA	NA	12	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N5K-C5548UP-FA	1	32 + expansion module	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	expansion module	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N5K-C5596UP-FA	2	48 + expansion module	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	expansion module	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N5K-C5672UP	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N5K-C56128P	2	48 + expansion module	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	expansion module	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N5K-C5596T-FA	2	32/16 + expansion module	RJ45/SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	expansion module	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N5K-C5624Q	1	12 + expansion module	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N5K-C5648Q	2	24 + expansion module	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N5K-C5696Q	4	expansion module	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N3K-C3048TP-1GE	1	48	RJ45	UTP28X*BU	NA	NA	NA	4	SFP+	PSF1PX**MBU	NA
N3K-C3172PQ-XL	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N3K-C3524P-10GX	1	24	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	NA	NA	NA	NA
N3K-C3548P-10GX	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	NA	NA	NA	NA
N3K-C31128PQ-10GE	2	96	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	8	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N3K-C31108PC-V	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6	QSFP+/QSFP28	PQSFP***MBU	FZTRL7N7NANM***
N3K-C3232C	1	32	QSFP+/QSFP28	PQSFP***MBU	PHQ4SFP***MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N3K-C3132Q-V	1	32	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N3K-C3264Q	2	64	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N3K-C3132Q-40GX	1	32	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N3K-C3164Q-40GE	2	64	QSFP+	PQSFPX**MBU	PHQ4SFPXA*MBL	FZ2ERLNLNSNM***	FZ8RL7NQSVMN***	NA	NA	NA	NA
N3K-C3172TQ-32T	1	32	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N3K-C3172TQ-XL	1	48	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N3K-C31108TC-V	1	48	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+/QSFP28	PQSFP***MBU	FZTRL7N7NANM***
N2K-C2348UPQ	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N2K-C2248PQ	1	48	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	4	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N2K-C2232PP	1	32	SFP+	PSF1PX**MBU	NA	FZ2ERLNLNSNM***	NA	8	SFP+	PSF1PX**MBU	NA
N2K-C2348TQ	1	48	RJ45	UTP28X*BU	NA	NA	NA	6	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N2K-C2332TQ	1	32	RJ45	UTP28X*BU	NA	NA	NA	4	QSFP+	PQSFPX**MBU	FZTRL7N7NANM***
N2K-C2232TM-E	1	32	RJ45	UTP28X*BU	NA	NA	NA	8	SFP+	PSF1PX**MBU	NA
N2K-C2232TM	1	32	RJ45	UTP28X*BU	NA	NA	NA	8	SFP+	PSF1PX**MBU	NA
N2K-C2224TP	1	24	RJ45	UTP28X*BU	NA	NA	NA	2	SFP+	PSF1PX**MBU	NA
N2K-C2248TP	1	48	RJ45	UTP28X*BU	NA	NA	NA	4	SFP+	PSF1PX**MBU	NA
N2K-C2248TP-E	1	48	RJ45	UTP28X*BU	NA	NA	NA	4	SFP+	PSF1PX**MBU	NA

Bold data represent 25/100GbE ports. UTP Copper parts * Length in feet. Fiber parts *** Length in meters. ^Cisco and Cisco Nexus are registered trademarks of Cisco Systems, Inc. and/or its affiliates in the United States and certain other countries.