


PANDUIT PART NUMBER	WEIGHT
FRIDT6X4	0.64 LB/EACH (288g/EACH)

**NOTES:**

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 6x4 3-PORT SPILL-OUT TO 1 1/2" I.D. CORRUGATED LOOM TUBING IS USED TO CREATE A 3-PORT FLEXIBLE SPILL-OUT INTO EQUIPMENT FRAMES OR TELECOMMUNICATIONS CABINETS. THE SPILL-OUT ACCEPTS THREE (3) PIECES OF 1 1/2" (38.1) I.D. SLIT CORRUGATED LOOM TUBING (CLT150F-X\*\*, CLT150F-T20)
3. THE FIBERRUNNER 6x4 3-PORT SPILL-OUT TO 1 1/2" I.D. CORRUGATED LOOM TUBING INCLUDES:  
ONE (1) 3-PORT SPILL-OUT HOUSING,  
ONE (1) 3-PORT SPILL-OUT RETAINER,  
ONE (1) 3-PORT SPILL-OUT HINGED DOOR
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D37617EC\_DC\_FRIDT6X4\_02.prt

CAD FILENAME/LAYERS FRIDT6X4.pdf

PANDUIT

CORP TINLEY PARK, ILLINOIS

FIBERRUNNER 6x4 3-PORT SPILL-OUT TO 1 1/2" I.D. CORRUGATED LOOM TUBING (FRIDT6X4)

CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.
---	---

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	GMBH
-	-	-	-	E. REVISED GENERAL NOTES D. REVISED CAD FILENAME	-	-	-		
2	7-6-06	MSO	RN	C. REVISED DRAWING TITLE B. REVISED AND REDRAWN	37617-95	RN	RN		

DRAWN BY MSO	MAT'L: ABS	SCALE NONE	DRAWING NO. 37617-95	DWG A SIZE
DATE 12-27-01	CHK'D WAB			