

QuickNet™ Tapped Fiber Optic Cassettes

technical information

Integral to the QuickNet Fiber Optic solution, fiber optic tapped cassettes are a highly effective and efficient means for mission-critical data centers and networks to obtain real-time network visibility. TAP cassettes provide passive optical tapping of live networks while maintaining full integrity of the data with no link downtime.

QuickNet TAP cassettes are designed for multimode applications and offer superior splitter technology to minimize loss, extend reach, and preserve signal integrity. The cassettes are offered in a variety of models to meet the demands of both structured cabling systems and dynamic situations. TAP cassettes facilitate monitoring of up to 48 duplex ports per one rack unit space and are suited for Opticom® Patch Panels, Enclosures, and Hardware, along with pre-terminated QuickNet Fiber products, for a complete end-to-end solution.



specifications

Fiber Type	Split Ratio	Split Loss Live/TAP	MTP* Connector	LC Connector
		(dB Loss at 850nm)	Insertion Loss (dB)	Insertion Loss (dB)
OM4	70/30	1.8/5.8	0.35	0.15

ordering information

Part Number	Top View	Front View	Rear View
FCT-7ZA		 6-Port Duplex LC TAP, 6-Port Duplex LC Live	 6-Port Duplex LC Live
FCT-7ZB		 6-Port Duplex LC TAP, 6-Port Duplex LC Live	 12-Fiber MTP* Live
FCT-7ZC		 4-Port Duplex LC Live, 4-Port Duplex LC Live, 4-Port Duplex LC TAP	Not Applicable
FCT-7ZD		 12-Port LC Duplex Live	 Two 12-Fiber MTP*s Live, Two 12-Fiber MTP*s TAP


*MTP ports are Male (pinned)

*MTP is a registered trademark of US Conec Ltd.


QuickNet™ Tapped Fiber Optic Cassettes

product dimensions


FCT-7ZA




FCT-7ZB



FCT-7ZC



FCT-7ZD



Dimensions are in inches. (Dimensions in parentheses are metric).

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

PANDUIT®

For more information
Visit us at www.panduit.com
Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2023 Panduit Corp.
ALL RIGHTS RESERVED.
FBSP87-WW-ENG
3/2023