

Smartzone™ 65



SmartZone™ G5 iPDU Value Proposition



3-Year standard and 5-Year extended warranty



 Built with premium components to withstand 140°F (60°C) at full load

High Temp



 Unique outlets design for high outlet density



Hot-Swappable and Upgradable

 Hot-Swappable Controller with large OLED display



 Enhanced security with certificate-based advanced asymmetric encryption, validated and hardened with multiple security scanning tools



1G Redundant Network Access

 Reduces deployment time and labor as PDU auto negotiates to 1GB network switches



 Real-time Monitoring of Power Environmental and Cabinet Security



Environmental Plug & Play Accessories

 Variety of Environmental and Cabinet Access Control Accessories



Multi-Device WebGUI

Enhanced User-Experience with a self adjusting WebGUI that senses the device you are on



 A variety of colored PDU chassis, power cords and cable ties

SmartZone™ G5 iPDU Families

Monitored Input (MI) Series

Input power monitoring.

Monitored Switched (MS) Series

Input power monitoring and outlet switching.

Monitored per Outlet (MPO) Series

Input and Outlet level power monitoring.

Monitored and Switched per Outlet (MSPO) Series


Input and Outlet level power monitoring and outlet switching.

Accessories

A variety of Environmental Sensors; Security Devices; and Power Cords.

Note: All intelligent PDUs Include capabilities for environmental monitoring and rack access control.

iPDU Key Features




SmartZone™ G5

Product Features	Monitored Input (MI)	Monitored Switched (MS)	Monitored per Outlet (MPO)	Monitored & Switched per Outlet (MSPO)
Design Features Low profile, space saving design Ultra low profile circuit breakers on most models Adjustable tool-less mounting system Color-coded receptacles Locking IEC receptacles and locking power cord compatible Symmetric vertical PDU Chassis to accommodate top or bottom power feed	•	•	•	•
PDU Energy Metering and Monitoring PDU level watt-hour energy metering (kWh) PDU level power measurements (W) Input Phase level power measurements (V, A, VA, kWh, pf) Circuit breaker level current measurements High-accuracy, billing-grade metering capabilities Embedded memory log to record/view/report historical data User customizable alarm thresholds & notifications	•	•	•	•
Environmental Management Optional Plug & Play environmental sensors including temperature, humidity, dry contact and water leak User customizable alarm thresholds and notifications	•	•	•	•
SmartZone™ Security Handle • Beacon LED to locate cabinets and provide automated visual indication for critical and warning alarms • Status LED provides visual indication of the handle and security status • Up to 200 Users for cabinet access • Multi-Frequency HID 125KHz/13.5MHz, Mifare & iClass • Dual Authentication (Keypad Version) • Field Replaceable Tumblers and Key (5 Options)	•	•	•	•
 Network Management and Local Display Interface Largest-in-class, high-visibility, OLED display Full featured network management and alerting capabilities supporting HTTP, HTTPS, SSH, Telnet, SNMP, FTP and email Strong encryption, passwords, and advanced authorization options including local permissions, LDAP, RADIUS, and Active Directory Daisy Chain up to 4 Rack PDUs and 32 environmental sensors through a single IP address 	•	•	•	•
Circuit Breaker Status Monitoring • Active monitoring and alarming of circuit breaker on/off status	•	•	•	•
Outlet Level Switching Remote On/Off power control by individual outlet User-defined power-on time delay to sequence IT equipment Automatic sequencing to avoid inrush current overload Outlet level user security with assignable roles and user access		•		•
Outlet Level Energy Metering Outlet level watt-hour energy metering (kWh) Outlet level power measurements (V,A,VA, W, pf) Outlet level information for Green Grid Level 3 PUE Calculations			•	•

Locking Outlets and Cables


- Locking outlets compatible to dual locking power cords
- Dual locking power cords provide locking at both end (PDU and equipment)
- Variety of power cords lengths and colors available














G5 Intelligent **Network Controller (iNC)**

(Hot Swappable)



Web GUI





Dashboard

Multi-Device Access




Desktop



Tablet




Smartphone



SmartZone™ Security Handle

Features

- · Up to 200 users
- · Multifrequency card access
- · HID 125KHz/13.5MHz, Mifare and iClass
- · Field replaceable tumbler and keys (five options)
- · Dual authentication (keypad version)





6

Accessories – SmartZone™ Security Handle

Specially designed accessories to connect directly to the SmartZone™ Security Handle. The SmartZone™ Security Handle features an integrated humidity sensor.

Environmental and Security





^{*}The MA030 features a coupler to optimize door removal and is 10 ft. (3m) in length.

Accessories - Environmental, Security and Power Cords

Security and Environmental Accessories that connect directly to the G5 iPDU, when NOT using SmartZone™ Security Handle

Environmental

- · Temperature (EA001)
- Temp + Humidity (EB001)
- · 3Temp + Humidity (EC001)
- · Rope Leak (ED001)
- · Spot Leak (EE001)
- · 3 Sensor Input Hub (EF001)
- Dry Contact Input (ACC01)









Security

- Door Contact Switch (ACA01)
- · Auto Light Bar (ACD01)



Power Cords

Dual Locking Power Cords







