THIS	COPY IS F	PROVID	DED ON	A REST	RICTED BA	SIS AND IS NOT TO BE USED IN ANY WAY DETRIMEN	TAL TO THE	INTE	RESTS	OF PANDUIT	CORP.				
						DIM	ensions -	- IN [r	mm]						
						COMPONENT	PART NUMBER								
LENGTH*						DESCRIPTION	HDW1/4-KT HDW3/8-KT HDW1/4-A-KT HDW3/8-A-KT QUANTITY				IDW3/8-A-KT				
	LL	NGIП				STAINLESS STEEL 1/4-20 HEX BOLT, 1.00 [25.4] LONG* INSTALLATION TOOL: 7/16" WRENCH	2	1	WA	2	N/A				
						STAINLESS STEEL 3/8-16 HEX BOLT, 1.00 [25.4] LONG* INSTALLATION TOOL: 9/16" WRENCH	N/A		2	N/A	2				
						STAINLESS STEEL 1/4-20 HEX NUT INSTALLATION TOOL: 9/16"	2	1	WA	2	N/A				
						STAINLESS STEEL 3/8-16 HEX NUT INSTALLATION TOOL: 9/16"	N/A		2	N/A	2				
						STAINLESS STEEL 1/4 FLAT WASHER	4	1	WA	4	N/A				
			(STAINLESS STEEL 3/8 FLAT WASHER	N/A		4	N/A	4				
					\leq	STAINLESS STEEL 1/4 BELLEVILLE COMPRESSION WASHER	2	1	N/A	2	N/A				
						STAINLESS STEEL 3/8 BELLEVILLE COMPRESSION WASHER	N/A		2	N/A	2				
						#12-24 THREAD FORMING SCREW, .45 [11.4] LONG** INSTALLATION TOOL: SLOTTED SCREWDRIVER / 5/16" WRENCH	2		2	N/A	N/A				
		LENG	TH** -			#10-32 THREAD FORMING SCREW, .45 [11.4] LONG** INSTALLATION TOOL: SLOTTED SCREWDRIVER / 5/16" WRENCH	N/A	1	₩A	2	2				
						M5 THREAD FORMING SCREW, 45 [11.4] LONG** INSTALLATION TOOL: SLOTTED SCREWDRIVER / 8mm WRENC	CH N/A	1	WA	2	2				
						M6 THREAD FORMING SCREW, .45 [11.4] LONG** INSTALLATION TOOL: SLOTTED SCREWDRIVER / 8mm WRENC	2		2	N/A	N/A				
									TITLE						
									STAINLESS STEEL HARDWARE KITS (HDW1/4-KT, HDW3/8-KT, HDW1/4-A-KT, HDW3/8-A-KT) CUSTOMER DRAWING						
		ļ							ITEM REVISI	ION NAME	N41736BB-C417	736/03	-		
									DATASET FILE NAME		C41736/03.SLE		HAN	DUI	T
									DIMEN	UNLESS OTHERWISE SPEC DIMENSIONAL TOLERANCES A		, I	MATERIAL		
			İ					X. XX.	± ±	.XXX <u>+</u> ANGLES <u>+</u>		SEE NOTES			
03	3/13	ЈНИЦ	ЈНИЦ			V41736BB-C4			$ \Rightarrow - $	THIRD A PROJEC		DRAWING NUMBER C41736_03			
REV	DATE	BY	СНК	APR		DESCRIPTION	ECN		drawn by JI	HNU		NONE	SHEE	T 1 OF 1	A