# PatchRunner™ 2 Horizontal **Cable Managers**



## **SPECIFICATIONS**

The high-capacity horizontal cable managers shall be a front only design capable of managing copper and fiber cables on any 19" EIA cabinet or rack. These managers shall be constructed with a molded plastic frame and fingers which incorporate a bend radius that protects the cable. The fingers shall be inset towards the rack to allow easy access to patch cords and terminations. Standard pass-through holes shall incorporate bend radius control. Magnetic, dual-hinged covers shall allow access to the cable pathway.



## TECHNICAL INFORMATION

Part Number	RU	Manager Height in. (mm)	Cover Height in. (mm)	Width in. (mm)	Depth in. (mm)
PR2HF1	1	1.7 (43)	1.8 (45)		
PR2HF2	2	3.5 (88)	3.6 (90)	19.0 (484)	7.9 (202)
PR2HF3	3	5.2 (133)	5.4 (135)		
PR2HF4	4	7.0 (177)	7.1 (179)		

## **KEY FEATURES AND BENEFITS**

Deep channel opening:	Manage more cables in less RU spaces			
Inset fingers:	Fingers slope inward offering greater access to network cabling for easier moves, adds, and changes			
Finger spacing:	Wide front finger openings easily accommodate Category 6A and Category 6 copper cables speeding installation and reducing maintenance costs			
Dual hinged magnetic cover:	Molded plastic cover opens 190 degrees to the top or bottom to provide complete access to the horizontal pathway without having to remove the cover			
Flush appearance with PatchRunner 2 and PatchRunner 2 Enhanced Vertical Cable Managers:	Used together to improve data center and telecommunication room aesthetics and maximize cable capacity			

## **APPLICATIONS**

PatchRunner 2 Horizontal Cable Managers provide an efficient way to manage high performance copper, fiber optic, or coaxial cables on any 19" rack or cabinet. Projection allows for alignment with PatchRunner 2 and PatchRunner 2 Enhanced Vertical Managers to maximize cable capacity. Fixed bend radius fingers organize and protect patch cords as they exit patch panels and as they transition into the vertical pathway. All these features combine to provide the user with a horizontal cable management solution that simplifies cable routing in a finished professional appearance. When used with Panduit patch panels, patch cords, vertical cable managers, and racks, the user receives a total system that satisfies functional and aesthetic requirements for data centers and telecommunications rooms.

#### PatchRunner 2 Horizontal Cable Managers

1 RU manager PR2HF1+ front only:

2 RU manager

front only: PR2HF2+

3 RU manager front only: PR2HF3+

4 RU manager front only: PR2HF4+

#### PatchRunner 2 Vertical Cable Managers with Doors

**Dual-sided** with two doors: PR2VD\*^+

**Dual-sided with** 

one door: PR2VSD\*^+ Single-sided with PR2VFD\*^+ one door:

#### PatchRunner 2 Enhanced Vertical Cable Managers with Doors

**Dual-sided with** PE2VD\*^+ two doors:

**Dual-sided with** PE2VSD\*^+ one door:

Single-sided with PE2VFD\*^+ one door:

#### Rack Systems

2-Post Rack with threaded rails,

R2P^+ 3" deep:

2-Post Rack with

R2P6S^+ threaded rails.

6" deep

4-Post Rack #12-24

R4P\*\*^+ threaded rails:

#### Accessories

Pass-through hole blanking plugs:

NM\*\*\*B

\*Width, in.: 06, 08, 10, 12 \*\*Depth other than 30 in.: 23, 36, 42 \*\*\*RU: 1, 2, 3, 4 ^Height, in.: 79, 96


+Color: WH (White)



All Part Numbers Compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to the United States.

## PatchRunner™ 2 Horizontal Cable Managers

## **ENGINEERING DRAWING**



1 R2P – 19" Standard EIA Rack 19" x 3", 45 RU

## PatchRunner™2 Vertical Cable Managers and Doors

- 22 PR2VD06 6" wide
- 2b PR2VD08 8" wide
- 2 PR2VD12 12" wide

## **Angled Modular Patch Panels**

- 33 CPPLA48WBLY 2 RU, 48-Port
- (3) CPPA48HDWBLY 1 RU, High Density 48 – Port

#### **Cable Management Accessories**

- PR2HF4 Cable Manager, 4 RU
- 5 CMT4 Trough, 4 RU
- 6 PR2VEP End Panel
- 7 PR2VWF Waterfall

**WORLDWIDE SUBSIDIARIES AND SALES OFFICES** 

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

