Mini-Com[™] 45mm × 45mm Adapters and Adapter Kits



specifications

45mm × 45mm adapters shall be available in various ports and style configurations including spring-shuttered doors that protect connectors from dust and debris when not in use, and a sloped design for bend radius control. Adapters shall be compatible with standard 45mm × 45mm openings. Mounting tabs allow adapters to mount sideways when required. All adapters shall accept Mini-Com™ Modules for copper, fibre, and audio/video installations.



technical information

Mounting options:	Adapters snap into standard 45mm × 45mm faceplate openings		
Number of ports:	1-port and 2-port configuration		
Packaging:	Adapter kits include CBFAW plus the designated insert; select kits include labels and label coversAdapters include a dedicated single piece product; select adapters include labels and label covers		

kev features and benefits

Modular	Accepts all Mini-Com™ Modules, which snap in and out for easy moves, adds, and changes	
Shuttered feature	Select adapters include spring-shuttered doors to prevent dust and debris from touching contacts when patch cords are not connected	
Lables and label covers	Select adapters include a label pocket and icon slots for easy identification	
Mounting flexibility	Mounting tabs allow product to securely mount sideways when required	
Sloped design	Select adapters are sloped, allowing proper bend radius control	

applications

Panduit[™] Mini-Com[™] adapters offer an aesthetic solution that complements work areas while offering modularity for installation flexibility. Mini-Com™ Adapters support all Mini-Com™ copper, fibre, and audio/video applications.

As part of a global workstation outlet solution offered by Panduit, Mini-Com™ 45mm × 45mm Adapters mount to select industry standard frames that have a 45mm × 45mm opening.

Panduit 45mm × 45mm adapters and adapter kits offer a variety of features: spring-shuttered doors to protect connections from dust and debris; single- or dual-port density; labelling and icon options; and sloped design for bend radius control.

Adapter Kits (Frame and ½-Size Insert)

Frame with 2-port flat insert: CFPFF2AW

1-port sloped.

shuttered insert: CFPFS1SAW

Frame with 2-port sloped insert:

CFPFS2AW

Frame with 2-port sloped shuttered insert:

CFPFS2SAW*

Frame with 2-port sloped, shuttered insert with labels:

CFP45LS2SAW

45mm × 45mm Adapters (One-Piece Design)

45mm × 45mm

CBFAW

1-port sloped. shuttered with label and icon slots:

CFPFLS1SAW

2-port sloped, shuttered with label and icon slots:

CFPFLS2SAW

22.5mm × 45mm Adapter

1-port shuttered: CFA1FSAW-X

Modules

All adapters can be used with Mini-Com Modules for copper, fibre, or audio/video applications. Visit www.panduit.com for the complete selection. Shuttered adapters are not suitable for use with any audio/video or fibre connector module that protrudes beyond the face of the insert.

Labels


See table on page 2

*Available in BL (Black)


Mini-Com[™] 45mm × 45mm Adapters and Adapter Kits

label options

	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label
CFPFLS1SAW CFPFLS2SAW	-	-	C150X030Y1C
CFP45LS2SAW	-	-	UILS8BW
CFA1FSAW-X	-	T031X000FJT‡	-
CFPFS2AW CFPFS2SAW	C125X030FJJ*	T031X000FJT‡	C125X030FJC*
CFPFS1SAW	C061X030FJJ*	T031X000FJT‡	C061X030FJC*



[‡] do not remove liner for non-adhesive



WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty



^{*}adhesive