

# 5-Day Delivery Program



## Opti-Core™ Fiber Optic Patch Cords and Pigtails

- Receive your fiber optic patch cords in 5 business days or less
- Orders received after 2 p.m. CST will be entered the next business day
- Delivered within 5 business days of order booking by Panduit Customer Service
- Delivered to “Ship To” address on the purchase order
- Minimum order quantity of 10 pieces (per part number)
- Maximum order quantity of 200 pieces (per part number)
- Continental USA and Canada only

### Fiber Optic Patch Cord and Pigtail Program Details

- Only the following list of patch cord part numbers are supported based on fiber, cable, and connector types

### Part Numbers

Part Number *** = length (m)	Fiber Type	Length (m)	Max. IL (Per Mated Pair)	Description
<a href="#">FX2ERLNLNSNM***</a>	OM3	001-015	0.15dB	LC-Duplex to LC-Duplex, OM3, 1.6mm, Riser, Aqua
<a href="#">FZ2ERLNLNSNM***</a>	OM4	001-015	0.15dB	LC-Duplex to LC-Duplex, OM4, 1.6mm, Riser, Aqua
<a href="#">F92ERLNLNSNM***</a>	OS2	001-015	0.25dB	LC-Duplex to LC-Duplex, OS2, 1.6mm, Riser, Yellow
<a href="#">FZ2RPU1U1ONM***</a>	OM4	001-015	0.15dB	Uniboot LC Duplex to Uniboot LC Duplex, OM4, Opt. IL, Plenum, Aqua
<a href="#">F92RPU1U1ONM***</a>	OS2	001-015	0.25dB	Uniboot LC Duplex to Uniboot LC Duplex, OS2, Opt. IL, Plenum, Yellow
<a href="#">F92ERQ1Q1SNM***</a>	OS2	001-015	0.25dB	Push-Pull LC-Duplex to Push-Pull LC-Duplex, OS2, Std. IL, Riser, Yellow
<a href="#">FX2ERQ1Q1SNM***</a>	OM3	001-015	0.15dB	Push-Pull LC-Duplex to Push-Pull LC-Duplex, OM3, Std. IL, Riser, Aqua
<a href="#">FZ2ERQ1Q1SNM***</a>	OM4	001-015	0.15dB	Push-Pull LC-Duplex to Push-Pull LC-Duplex, OM4, Std. IL, Riser, Aqua
<a href="#">FX1BN1NNSNM001</a>	OM3	1	0.15dB	LC Buffered Fiber Pigtail, OM3, 900µm, 1m, Blue
<a href="#">FZ1BN1NNSNM001</a>	OM4	1	0.15dB	LC Buffered Fiber Pigtail, OM4, 900µm, 1m, Blue
<a href="#">F91BN1NNSNM001</a>	OS2	1	0.25dB	LC Buffered Fiber Pigtail, OS2, 900µm, 1m, Blue

# 5-Day Delivery

## Other Considerations

- Pricing – There is no difference to the pricing offered for this program

## Competitor Cross-Reference

Panduit Part Number	Corning Part Number	Commscope Part Number
<b>FX2ERLNLNSNM***</b>	050502T5116***M	N/A
<b>FZ2ERLNLNSNM***</b>	050502Q5116***M	FEXLCLC42-MX***
<b>F92ERLNLNSNM***</b>	040402R5116**M	FEWLCLC42-JXM***
<b>F92RPU1U1ONM***</b>	787802GD1200***M	UFGLLULUK2-JXM***
<b>FZ2RPU1U1ONM***</b>	797902QD1200***M	UFXLULUK2-MXM***
<b>FX1BN1NNNSNM001</b>	000301T4180001M	N/A
<b>FZ1BN1NNNSNM001</b>	00301Q4190001M	FBXLCUC11-MXM001
<b>F91BN1NNNSNM001</b>	000201R4131001M	FBWLCUC11JXM001