
THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



CT-3001/CCPBT, 6.7 TON MULTI-USE (CRIMP-CUT-PUNCH) TOOL

This tool meets requirements for Safety for Handheld Motor-Operated Electric Tools specification UL 60745-1 and CSA C22.2 No. 60745-1.

Tool is listed under CSA file number 80103907. Tool meets OSHA mandated electrical and mechanical product safety requirements.

GENERAL NOTES

1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.

2. DIMENSIONS IN [] ARE METRIC.

3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF ROHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE ROHS TECHNICAL ADAPTATION COMMITEE.

TOOL SPECIFIC NOTES:

- 1. THE CT-3001/CCPBT BATTERY OPERATED MULTI-USE TOOLS ARE DESIGNED TO CRIMP, CUT AND PUNCH (WITH ACCESSORIES.)
- THE TOOL CRIMPS PANDUIT COPPER AND ALUMINUM COMPRESSION CONNECTORS USING PANDUIT CRIMPING DIES. GO TO www.panduit.com FOR MORE INFORMATION.
- THE TOOL CUTS ALUMINUM AND COPPER CODE CONDUCTOR CABLE UP TO 1" [25mm].
- THE TOOL CUTS ALUMINUM AND MILD STEEL THREADED ROD;
- M5 TO M12, AND 1/4 TO 1/2 UNC THREAD.

 5. PUNCH CAPACITY OF 2" [50 mm] CONDUIT SIZE IN 10 GAUGE [3.41 mm] MILD STEEL WITH STANDARD GREENLEE PUNCHES AND PANDUIT PUNCH DRIVE ADAPTER.
- THIS TOOL CAN OPERATE WITH BLUE TOOTH TECHNOLOGY TO CONNECT TO THE I-PRESS PHONE APP TO MONITOR CRIMP PERFORMANCE.

THE CT-3001/CCPBT TOOL KIT INCLUDES: QTY. DESCRIPTION/ITEM

- BATTERY OPERATED 6.7 TON HYDRAULIC MULT-USE (CRIMP, CUT
- RECHARGEABLE BATTERIES (MAKITA LITHIUM-ION 18VDC, 4Ah)
- MAKITA BATTERY CHARGER 120VAC (WITH US PLUG CONFIGURATION)

TOOL CASE

SET OF "UAW" DIE ADAPTERS

TECHNICAL INFORMATION:

1. TOOL WEIGHT (INCLUDING BATTERY) 7.1 LBS. [3.2 kg] 2. DIMENSIONS (INCLUDING BATTERY) 18.7" L × 4.6" H × 3.0" W $[475 L \times 116 H \times 75 W] mm$

3. CRIMPING FORCE 6.7 TONS [60 kN]

- 4. TOOLS ARE TO BE USED WITH PANDUIT CRIMP DIES, CABLE CUTTERS, THREADED ROD CUTTERS AND PUNCH DRIVE ADAPTERS AND ARE SOLD
- SEPARATELY. (GO TO www.panduit.com FOR MORE INFORMATION.)

 5. "UAM" ADAPTER FOR CABLE CUTTING APPLICATIONS IS SOLD SEPARATELY.

 6. A COPY OF OPERATION MANUAL AND ACCESSORY INFORMATION CAN

BE FOUND AT: www.panduit.com.

DIMENSIONS IN [BRACKETS] ARE IN MILLIMETERS. ALL DIMENSIONS ARE FOR REFERENCE ONLY.

PART NUMBER

