

2

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

	PART NO.	DESCRIPTION	DUAL HINGE DOOR	SPLIT DOOR	SINGLE HINGE DOOR	SPLIT SIDE PANEL	CAGE NUT E-RAIL (2-SETS)	TAPPED E-RAIL (2-SETS)	CABLE MANAGEMENT	CABINET WEIGHT FULLY UNPACKAGED	CABINET WEIGHT SHIPPING WEIGHT
	N8212*T	NET-ACCESS N-TYPE CABINET 42RUX1070mm DEEP	01	01	00	02	00	01	02	144 Kg/EACH 318 LBS/EACH	165 Kg/EACH 363 LBS/EACH
	N8512*T	NET-ACCESS N-TYPE CABINET 45RUX1070mm DEEP	01	01	00	02	00	01	02	150 Kg/EACH 332 LBS/EACH	171 Kg/EACH 377 LBS/EACH
	N8812*T	NET-ACCESS N-TYPE CABINET 48RUX1070mm DEEP	01	01	00	02	00	01	02	159 Kg/EACH 350 LBS/EACH	179 Kg/EACH 395 LBS/EACH
	N8219*T	NET-ACCESS N-TYPE CABINET 42RUX1070mm DEEP	01	01	00	00	00	01	02	106 Kg/EACH 235 LBS/EACH	127 Kg/EACH 280 LBS/EACH
	N8519*T	NET-ACCESS N-TYPE CABINET 45RUX1070mm DEEP	01	01	00	00	00	01	02	113 Kg/EACH 250 LBS/EACH	134 Kg/EACH 295 LBS/EACH
	N8819*T	NET-ACCESS N-TYPE CABINET 48RUX1070mm DEEP	01	01	00	00	00	01	02	120 Kg/EACH 265 LBS/EACH	141 Kg/EACH 310 LBS/EACH

В

\* DENOTES COLOR

"B" = BLACK

В

₩₩ = WHITE

TITLE NET-ACCESS N TYPE CABINET WITH INTEGRAL CABINET TOP CABLE ROUTING Α A SYSTEM 800mm WIDE X 1070mm DEEP FAMILY CUSTOMER DRAWING ITEM REVISION NAME 12V352AV/01.PRT PANDUIT DATASET FILE NAME 12V352AV\_DC/01A.PRT MATERIAL: N/A 01A 12-09-14 PBS ADP V09000BX TCN SEE SHEET 1 OF 5 FOR REVISIONS DRAWING NUMBER: THIRD ANGLE 00A 4-01-13 PBS NAGL JDWE 12V352AV-DC 12V352AV-DC SEE SHEET 1 OF 5 FOR REVISIONS PROJECTION SCALE SIZE DRAWN BY DATE СНК REV DATE СНК APR ECN ΒY DESCRIPTION PBS 4-01-14 NAGL NONE SHT 2 OF 5

1

2





