
Strain Relief Bar with Direct Patch Panel Mount and Quick Release Bracket



specifications

Strain relief bar shall consist of a metal bar that attaches directly to most Panduit patch panels through the use of a quick-release bracket. Once assembled to a patch panel, it shall provide front and rear access to the panel, allowing patch panel to be mounted or removed from the front of a standard EIA 19" rack or cabinet. Ideal for installations with only single rails where standard strain relief bars have limited mounting options.



Direct Mount Strain Relief Bar/Brackets

Bar with bracket: SRBPPQBRKT

For use with all Panduit patch panels except flat QuickNet® Panels and NetKey® Molded Patch Panels.

technical information

Mounting options:	Mounts directly to standard 19" patch panels
Packaging:	Kit includes a strain relief bar with integrated cable tie mounts and a set of brackets (left and right), and cable ties to secure individual cables

key features and benefits


Patch panel mounting	Mounts directly to most Panduit patch panels enabling the panel and strain relief bar to be simultaneously mounted or removed as one unified component keeping all cables connected in place
Built in cascade	Provides smooth resting surface for cable routing to help maintain network integrity
Cable tie mounts	Secure individual cables
Quick release brackets	Enables strain relief bar to be removed or re-installed without having to remove the patch panel; no tools needed

applications

Strain relief bars are used to support, manage, and organize cables in telecommunication rooms. Unique design is compatible with most Panduit patch panels allowing the panel and bar to be mounted through the front of a standard 19" rack or cabinet as an integrated unit. The bar can also be installed through the back of the rack by snapping it on to the panel

via the pre-installed brackets. Quick release brackets allow the strain relief bar to be removed and replaced quickly without disturbing the patch panel or the need to use a tool. Panduit strain relief bars contribute to network integrity and reduce time and cost associated with cable routing and maintenance.

Strain Relief Bar with Direct Patch Panel Mount and Quick Release Bracket



Dimensions are in inches [Dimensions in brackets are metric]

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300

PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty





Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2013 Panduit Corp. ALL RIGHTS RESERVED. COSP320--WW-ENG 9/2013

