IndustrialNet[™] M12 D-Code to RJ45 Panel Mount Adapter

specifications

M12 D-code to RJ45 industrial adapters shall be applicable for use in manufacturing as well as other industrial environments and shall meet or exceed the requirements of the ANSI/TIA-568-C.2 Category 5e, ISO 11801 Class D, IEC 61076-2-101 and ODVA Ethernet/IP and PROFINET standards. The adapter housing shall be constructed of Nylon GF. The adapter shall incorporate an ingress protection rating of IP20 on the RJ45 side and IP68 on the M12 side when mated. The adapter shall offer an extended temperature range as required for more demanding applications. The adapter shall be easily field installable without any special tools.

technical information

Electrical/ mechanical performance:	Exceeds channel requirements of ANSI/TIA-568-C.2 Category 5e and ISO 11801 Class D at swept frequencies up to 100MHz meets the requirements of IEC 61076-2-101 and the ODVA Ethernet/IP^ and PROFINET standards
IEC compliance:	Meets IEC 61076-2-101
IP compliance:	Rated IP20 (RJ45) and IP68 (M12 side)
RoHS compliancy status:	Compliant
Temperature rating:	Operating -25°C to 80°C (-13°F to 176°F) Storage -40°C to 80°C (-40°F to 176°F)
Packaging:	1 unit per PE bag, 10 units per carton

key features and benefits

Robust construction	Nylon GF housing with full 360° shielding for secure data transmission in high noise (EMI/RFI) environments, exceed the requirements of IEC 61076-2-101 for vibration, mating cycles, and insertion/withdrawal force
Field attachable	Can be assembled without any special tools
Extended temperature range	Operating -25°C to 80°C (-13°F to 176°F)

SPECIFICATION SHEET

IndustrialNet [™] M12 D-Code to **RJ45 Panel Mount Adapter** Panel mount adapter: ICAM12DRJS IndustrialNet [™] Category 5e SF/UTP Copper Cable CM 4-pair: ISFCH5C04A*-XG IndustrialNet[™] Category 5e F/UTP Copper Cable CM 4-pair/ color Black: IFC5C04BBL-CEG IndustrialNet[™] Category 5e U/UTP Copper Cable CM 4-pair/ color Black: IUC5C04ABL-CEG IndustrialNet [™] Category 6 F/UTP Copper Cable CM 4-pair/ color Black: IFC6C04BBL-CEG IndustrialNet[™] Category 6 U/UTP Copper Cable CM 4-pair/ color Black: IUC6C04ABL-CEG IndustrialNet[™] Category 6/5e RJ45 Field Terminable Plug Field ISPS688FA terminable plug: IndustrialNet [™] M12 D-Code Field **Terminable Plug** Field terminable plug: ISPS5E44MFA IndustrialNet[™] Category 5e Shielded 600 V-Rated Patch Cords **ISTPHCH1MTL CM/CMX: Mini-Com[®] Modular Patch Panel 8-port: CDPP8RG DIN Rail Adapter 1-port: CADIN1IW***

applications

IndustrialNet[™] adapters provide an ideal solution to support Industrial Ethernet from the Local Area Network (LAN) based support offices to the processing devices on the plant floor. The M12 D-code to RJ45 industrial adapter is a key component to an overall Industrial Ethernet application. The adapter will be the interface that protects the integrity of the Ethernet data transfer from the switch or PLC out to the devices or up to the horizontal plant backbone. The adapter is of a nylon GF construction and fully shielded for use in high noise (EMI/RFI) environments. The adapter is easily field installable for on-site installation and also offers an extended temperature range -25°C to 80°C (-13°F to 176°F) for use in more demanding applications such as manufacturing facilities where temperature extremes are the norm. *To designate color, add suffix TL (Teal), BL (Black), RD (Red), BU (Blue), GY (Gray), or YL (Yellow).

**For other lengths, change the length designation (1M) of the part number to the desired length (0.3M, 0.6M, 2M, 3M, 5M, or 10M); to designate color, replace TL (Teal) suffix with BL (Black), RD (Red), or YL (Yellow). For example, the part number of a 2-meter teal patch cord is ISTPHCH2MTL.

***For standard colors other than Off White, replace IW in part number with BL (Black), EI (Electric Ivory), IG (International Gray), or WH (White).


^EtherNet/IP is a trademark of ODVA.

www.panduit.com



PROFI

IndustrialNet[™] M12 D-Code to RJ45 Panel Mount Adapter



Dimensions are in inches. [Dimensions in brackets are metric].

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575

PANDUIT JAPAN PAN Tokyo, Japan Gua Phone: 81.3.6863.6000 Pho

PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information



Visit us at www.panduit.com

iai@panduit.com

©2018 Panduit Corp. ALL RIGHTS RESERVED. COSP337--WW-ENG 5/2018