




2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. DESIGNED FOR MOUNTING ON 19" EIA RACKS.
2. COMPONENTS:
1- MANAGER
2- 17" DUAL HINGED COVERS
4- #12-24 x 1/2" SCREWS
2- STRAIN RELIEF CLIPS
3. DIMENSIONS IN PARENTHESES ARE METRIC.

MAX STORAGE TEMPERATURE 65°C (149°F)
MAX OPERATING TEMPERATURE 60°C (140°F)



PANDUIT P/N	WEIGHT
WMPLSE	1.9 lbs/EACH 862 g/EACH

TITLE										
WMPLSE HORIZONTAL MANAGER										
CUSTOMER DRAWING										
ITEM REVISION NAME					V10101LS/08					
DATASET FILE NAME					V10101LS_DC/08A					
					THIRD ANGLE PROJECTION					
MATERIAL					ABS					
DRAWING NUMBER					10101-22					
DRAWN BY					DATE		CHK		SCALE	
JDWE					12-17-02		MECA		NONE	
SHEET 1 OF 1					A					

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
08A	3-23-23	JBO	KRKE	KCOR	UPDATED COVER TO CURRENT LOGO INCREASED SIZE OF TRI VIEW	M09000SE

2

1

B

A

A-SIZE CUSTOMER