### **Wyr-Grid Cabinet Mount Bracket**





Part Number(s): WGCMB1070\*\*, WGCMB1200\*\*, WGCMK1070\*\*, & WGCMK1200\*\*

© Panduit Corp. 2014


#### **INSTALLATION INSTRUCTIONS**

V00029FB






Note: The cabinet Mounting Brackets in the depicted configurations are capable of supporting Wyr-Grid Pathways at their safe working load unless otherwise noted.




(See page 5 & 6 for Pathway installation.)


## Standard Elevated Installation wgcmk1070\*\* or wgcmk1200\*\* (as shown)



Step 1: Attach adjustable legs to top of cabinet using (2) M5 Torx Screws. (each leg) (Do not tighten M5 Torx screws)



Step 2: Attach Strut to top of adjustable legs using (1) M10 Bolt & (1) M10 lockwasher per side. Square the adjustable legs and tighten the M10 Bolts & M5 Torx Screws (1.6 Lb-ft / 2.1 N-m).




Step 3: Adjust the height of the Strut to the desired height.


Height Adjusts from 11.00" (279.4mm) to 16.75" (425.5mm)


Torque Screws to a min. of 4 Lb-ft (5.4 N-m) per screw.

(See page 5 & 6 for Pathway installation.)



#### **Top Integral Cable Manager Installation**







Step 3: Re-install Front and Rear Fascias

(See page 5 & 6 for Pathway installation.)

#### VED Top Integral Cable Manager Installation (WGCMB1070\*\* is required for this application)






## **Wyr-Grid Center Support Installation**


Step 1: Loosen clips & slide clips outside the pathway's width.

Step 2: Install the Center Support in the desired location by inserting the Support in the strut parallel with the front of the cabinet & rotating 1/4 turn.




FR716DR

# Wyr-Grid WG8\*\*10, WG12\*\*10, WG18\*\*10, WG24\*\*10, & WG30\*\*10 Installation



Step 1: Position Wyr-Grid & place clips over the pathways wires.




Step 2: Tighten both clips to 4 Lb-ft (5.4 N-m)


For Technical Support: www.panduit.com/resources/install\_maintain.asp

#### FiberRunner FR4X4\*\*6, FR6X4\*\*6, & FR12X4\*\*6 Installation

NOTE: For FR24X4\*\*6 Clips must be rotated 180°



Step 3: Tighten both clips to 4 Lb-ft (5.4 N-m)



For Instructions in Local Languages and Technical Support:

 $www.panduit.com/resources/install\_maintain.asp$ 



E-mail: techsupport@panduit.com Phone: 866-405-6654