



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




#### NOTES:



1. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
2. DIMENSIONS IN [ ] ARE METRIC.
3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
4. WEIGHT: 19 lbs [9 kg]
5. PART INCLUDES:
  - 1- FIXED CASTER AND BRACKET ASSEMBLY
  - 1- SWIVEL CASTER AND BRACKET ASSEMBLY
  - 4- 3/8-16 x 1" HEX HEAD BOLT
  - 4- 3/8-16 HEX NUT
  - 8- 3/8" INTERNAL TOOTH LOCKWASHER
  - 4- FLOOR ATTACHMENT BRACKETS
  - 1- INSTRUCTION SHEET
6. DYNAMIC LOAD RATING: 2,500 lbs




SWIVEL CASTER AND  
BRACKET ASSEMBLY



FIXED CASTER AND  
BRACKET ASSEMBLY



PART NUMBER		RCSTR	
TITLE		CASTER BRACKET KIT FOR R4P% 4-POST RACKS	
CUSTOMER DRAWING			
ITEM REVISION NAME		V10679EL/04	
DATASET FILE NAME		V10679EL_DC/04A	
		THIRD ANGLE PROJECTION	
MATERIAL		STEEL	
DRAWING NUMBER		V10679EL - DC	
DRAWN BY	DATE	CHK	SCALE
PM	03-01-10	SRK	NONE
SHEET 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	04/03/23	TWV	MPOL	KCOR	ADDED STATIC LOAD RATING	V10679EL