

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

**NOTES, UNLESS OTHERWISE SPECIFIED:**


**FULLY AUTOMATIC PUMP SPECIFICATIONS**

MOTOR:

Type: Commutator  
 RPM: 1200  
 Voltage: AC 120V  
 Frequency: 50/60 Hz  
 Current: 6.5A  
 Horsepower: 1/2

PUMP:

Low Pressure: 20kg/cm<sup>2</sup> (300 psi)  
 Delivery: 2.6 Liters/Min.  
 High Pressure: 600 Kg/cm<sup>2</sup> (10,000 psi)  
 Delivery: .32 Liters/Min.  
 Oil Tank Cap.: 2 Liters  
 Weight: 15 kg (33 lbs.)  
 Fluid Type: EP Hydraulic Oil 32MV  
 Housing Color: Orange



**SEE SHEET 2 FOR FEATURES**

F:\wrkgrp\rvusers\ENGR DOCS-NEW\CUST DWGS\TP24507A01\_01 CT-901HP CD.doc



CORP. TINLEY PARK, ILLINOIS

**CT-901HP\*CUSTOMER DRAWING**

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:

(.x) ± --- (.xxx) ± ---  
 (.xx) ± --- ANGLES ± ---

UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY:  
BLR

MATL:

SCALE

**NONE**

DATE:  
8-03-07

-----

DRAWING NO.

DWG  
**A**  
SIZE

CHK'D:  
BJPU

**TP24507A01**

01	8-03-07	BLR	BJPU	REDRAWN	4255	--	JRWA	
REV	DATE	BY	CHK'D	DESCRIPTION	ECN	-R	CUST	SUP

