

## Pan-Ty® Cable Ties – Nylon 6.6

- For indoor use
- Versatile locking cable ties can be used in countless applications
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



Part No.	Cross-Section	Color	Size Length x Width x Thickness	Max. Bundle Diameter	Min. Loop Tensile Str.	Recommended Installation Tool	Pkg. Qty.
PLT2H-L	Light-heavy	Natural	8.1" x 0.300" x 0.075"	2"	120 lbs.	GTH-E, GS4H, GS4EH, PTH, STH2, ST3EH	50
PLT1.5I-M	Intermediate	Natural	5.6" x 0.142" x 0.045"	1.38"	40 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	1000
PLT1.5I-M0	Intermediate	Black	5.6" x 0.142" x 0.045"	1.38"	40 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	1000
PLT1.5M-M	Miniature	Natural	5.6" x 0.098" x 0.043"	1.25"	18 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	1000
PLT1.5S-M	Standard	Natural	6.2" x 0.190" x 0.052"	1.5"	50 lbs.	GTS-E, GS2B, GTH-E, PTS, PPTS, PTH, STS2, STH2	1000
PLT1.5S-M0	Standard	Black	6.2" x 0.190" x 0.052"	1.5"	50 lbs.	GTS-E, GS2B, GTH-E, PTS, PPTS, PTH, STS2, STH2	1000
PLT2S-M	Standard	Natural	7.4" x 0.190" x 0.052"	1.88"	50 lbs.	GTS-E, GS2B, GTH-E, GS4H, PTS, PPTS, PTH, STS2, STH2	1000
PLT2S-M0	Standard	Black	7.4" x 0.190" x 0.052"	1.88"	50 lbs.	GTS-E, GS2B, GTH-E, GS4H, PTS, PPTS, PTH, STS2, STH2	1000
PLT3S-M	Standard	Natural	11.5" x 0.190" x 0.052"	3"	50 lbs.	GTS-E, GS2B, GTH-E, GS4H, PTS, PPTS, PTH, STS2, STH2	1000

## Pan-Ty® Marker and Flag Ties

- Nylon 6.6 material for indoor use
- Weather resistant material has greater resistance to damage caused by ultraviolet light – indoor or outdoor use
- Flame retardant material has a flammability rating of UL 94V-0 – for indoor use
- Used to fasten and identify bundles at the same time
- One-piece construction for consistent performance and reliability
- Can be marked with Panduit marker pens or computer printable labels
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



Part No.	Cross-Section	Color	Marker Type	Size Length x Width x Thickness	Marker Write-On Area	Max. Bundle Diameter	Min. Loop Tensile Str.	Recommended Installation Tool	Pkg. Qty.
PLF1M-C	Miniature	Natural	Flag	4.3" x 0.98" x 0.45"	0.31" x 0.75"	0.87"	18 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	100
PLM2M-C	Miniature	Natural	Wrap	8" x 0.98" x 0.35"	0.26" x 0.95"	2"	18 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	100
PLM2S-C	Standard	Natural	Wrap	7.4" x 0.185" x 0.52"	0.44" x 0.87"	1.75"	50 lbs.	GTS-E, GS2B, GTH-E, GS4H, PTS, PTH, PPTS, STS2, STH2	100

## Pan-Steel® Polyester Fully Coated Cable Ties – MLTFC Series

- Polyester coating available in two color options provides visual indication for easy identification
- Self-locking head design speeds installation and locks into place at any length along the tie body
- Heavy cross section
- Polyester coating provides additional edge protection and prevents corrosion between dissimilar metals
- AISI 316 stainless steel for the most corrosive environments
- UV resistant, low smoke, halogen-free material
- Temperature Range: -40° to 302°F



MLTFC2H-LP316RD



MLTFC2H-LP316BU

Part No.	Color	Size Length* x Width x Thickness ^	Max./Min. Bundle Diameter	Min. Loop Tensile Str.	Recommended Installation Tool	Pkg. Qty.
MLTFC2H-LP316RD	Red	7.9" x 0.31" x 0.010"	2"/0.5"	250 lbs.	GS4MT, ST2MT HTMT, PPTMT, PBTMT	50
MLTFC2H-LP316BU	Blue	7.9" x 0.31" x 0.010"	2"/0.5"	250 lbs.	GS4MT, ST2MT HTMT, PPTMT, PBTMT	50

\*Other lengths available, contact Panduit Customer Service.

^ Base material less coating.

**Pan-Ty® Locking Cable Ties – Polypropylene – Distinctive Green Color**

- For chemical resistance where high loop tensile strength is not required especially in the presence of hydrochloric acid, salts, and bases
- For indoor use
- Material requires lowering the tool setting (see table below)
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



Part No.	Cross-Section	Color	Size Length x Width x Thickness	Max. Bundle Diameter	Min. Loop Tensile Str.	Recommended Installation Tool	Tool Setting	Pkg. Qty.
PLT1M-M109	Miniature	Green	3.9" x 0.098" x 0.043"	0.87"	11 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	2	1000

**Pan-Ty® Releasable Cable Ties – Nylon 6.6**

- For indoor use
- Extended release tab permits easy release and re-use where changes are anticipated during development, production, or servicing in the field
- One-piece construction for consistent performance and reliability
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation
- UL Listed for use in plenum or air handling spaces per NEC



Part No.	Cross-Section	Color	Size Length x Width x Thickness	Max. Bundle Diameter	Min. Loop Tensile Str.	Recommended Installation Tool	Pkg. Qty.
PRT2S-C	Standard	Natural	7.4" x 0.190" x 0.52"	1.88"	50 lbs.	Hand install only	100

**Pan-Ty® Clamp Ties – Nylon 6.6**

- For indoor use
- Used to secure a cable bundle to another surface such as a control panel, communication rack, wall or ceiling
- Design allows for bundling before or after screwing clamp in place
- One-piece construction for consistent performance and reliability
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation
- UL Listed for use in plenum or air handling spaces per NEC



PLC1M-S4-C

Part No.	Cross-Section	Color	Size Length x Width x Thickness	Nominal Hole Dia.	Screw Size	Metric Screw Size	Max. Bundle Diameter	Min. Loop Tensile Str.	Recommended Installation Tool	Pkg. Qty.
PLC1M-S4-C	Miniature	Natural	4.3" x 0.100" x 0.45"	0.122"	#4	M2.5	0.75"	18 lbs.	GTS-E, GS2B, PTS, PPTS, STS2	100
PLC2S-S6-C	Standard	Natural	7.9" x 0.190" x 0.47"	0.148"	#6	M3	1.84"	50 lbs.	GTS-E, GS2B, GTH-E, GS4H, PTS, PTH, PPTS, STS2, STH2	100

### Cable Tie Tools – Tool Controlled Tension and Cut-Off

- Use in production, maintenance, or construction applications
- Tool controls tension provides flush cut-off and speeds installation to lower installed cost
- Lightweight and balanced
- Easy to change tension adjustment and easy to operate
- A combination of design, operation, and construction features, provides a long service life
- No special maintenance required
- Ergonomic design lowers the risk of repetitive motion injuries
- Lowest activation and impact to installer's hand



Part No.	Weight	Use with Cable Ties
GTS-E	9.8 oz.	SM, M, I, S
GTH-E	12 oz.	S, HS, LH, H

### Mounts, Plates and Spacers

We carry mounts, plates and spacers. Go to [www.panduit.com](http://www.panduit.com) for our full offering.



### 4-Way Adhesive Backed Cable Tie Mounts

- Allows cable tie entry from all four sides
- Available in multiple sizes to match application load requirements
- Provides 2-up for fast and easy liner removal to speed installation

#### Rubber Adhesive

- General purpose
- Fast strength adhesion dwell time 2 hours after installation, prior to loading
- Temperature Range: -20° to 120°F

#### Acrylic Adhesive

- For high temperature locations and exposure to UV rays
- Maximum adhesive strength after 8 hours dwell time, prior to loading
- Temperature Range: -20° to 180°F




Part No.	Size Length x Width x Thickness	Material	Color	Environment	Adhesive Mounting Method	Used with Cable Ties*	Pkg. Qty.
ABMM-A-C	0.75" x 0.75" x 0.18"	ABS	White	Indoors	Rubber	M, I	100
ABMM-AT-C0	0.75" x 0.75" x 0.18"	Weather Resistant ABS	Black	Outdoors/HighTemp	Acrylic	M, I	100
ABM2S-A-C	1.00" x 1.00" x 0.16"	ABS	White	Indoors	Rubber	M, I, S	100
ABM2S-AT-C0	1.00" x 1.00" x 0.16"	Weather Resistant ABS	Black	Outdoors/HighTemp	Acrylic	M, I, S	100
ABM112-A-C	1.12" x 1.12" x 0.16"	Nylon 6.6	White	Indoors	Rubber	M, I, S	100
ABM112-AT-C0	1.12" x 1.12" x 0.16"	Weather Resistant Nylon 6.6	Black	Outdoors/HighTemp	Acrylic	M, I, S	100
ABM3H-A-L	1.50" x 1.50" x 0.25"	Nylon 6.6	White	Indoors	Rubber	M, I, S, HS, LH, H, HLM	50
ABM3H-AT-L	1.50" x 1.50" x 0.25"	Nylon 6.6	White	Indoors/HighTemp	Acrylic	M, I, S, HS, LH, H, HLM	50
ABM4H-A-L	2.00" x 2.00" x 0.25"	Nylon 6.6	White	Indoors	Rubber	M, I, S, HS, LH, H, HLM	50
ABM4H-AT-L	2.00" x 2.00" x 0.25"	Nylon 6.6	White	Indoors/HighTemp	Acrylic	M, I, S, HS, LH, H, HLM	50

\*Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, and H = Heavy, HLM = Miniature Tak-Ty® Hook & Loop Ties.

### Adhesive Backed Latching Wire Clips

- Route and secure cords and cables
- Convenient releasable latch
- Available in three sizes with releasable latch
- For indoor use only
- Gray Color Nylon 6.6\*
- Rubber adhesive



Part No.	Size	Max. Bundle Diameter	Pkg. Qty.
LWC38-A-C	1"L x 1"W x 0.56"H	0.38"	100
LWC50-A-L	1.26"L x 1"W x 0.67"H	0.50"	50
LWC75-A-L	1.48"L x 1.24"W x 0.9"H	0.75"	50

\*Go to panduit.com for full product offering. Gray wire clips pictured.

### Clincher™ Adjustable Releasable Clamp

- Adjustable clamp designed to contain a range of cable bundle diameters
- Latch can be released to provide access to cable bundles
- For indoor use only
- Material: Polypropylene
- Bundle Diameter Range: 0.19"-0.68"
- Rubber adhesive:
  - General purpose choice with fast strength adhesion dwell time of 2 hours after installation, prior to loading.
  - Temperature range: -20° to 120°F
- Gray
- 25/Pkg.



### Bevel Entry Clips

- Beveled entry allows for easy insertion of cable bundle
- Natural Color Nylon 6.6
- For indoor use only
- Rubber adhesive
- 50/Pkg.



Part No.	Size	Max. Bundle Diameter
BEC38-A-L	1.46"L x 1.24"W x 0.52"H	0.38"
BEC62-A-L	1.46"L x 1.24"W x 0.79"H	0.62"
BEC75-A-L	1.46"L x 1.49"W x 0.89"H	0.75"

### Adhesive Backed Cord Clips

- Cables are easily snapped into or out of the clips
- Natural Color Nylon 6.6
- Rubber adhesive
- 100/Pkg.



Part No.	Size	Max. Bundle Diameter
ACC19-A-C	0.75"W x 0.62"L x 0.25"H	0.19"
ACC38-A-C	1.00"W x 1.00"L x 0.38"H	0.38"
ACC62-A-C	1.24"W x 1.12"L x 0.63"H	0.62"

### Pan-Steel® Strapping – MS Series

- Fold over design provides high-retained tension in mechanical fastening and cable bundling applications
- Can be used in a wide range of indoor, outdoor, and underground (including direct burial) applications
- Smooth surfaces and rounded edges assures cable protection and worker safety
- AISI 201 stainless steel for general-purpose applications
- AISI 316 stainless steel for the most corrosive environments
- After tensioning, cut end is locked inside with low profile buckle – no sharp edges
- Recommended installation tool – BT75SDT

Part No.	Description	Size Length* x Width x Thickness	Max./Min Bundle Diameter	Strap Breaking Strength	Pkg. Qty.
MS4W75T30-Q2	Stainless steel strapping, 201 AISI stainless steel	20.2"L x 0.75"W x 0.030"T	4"/1"	2400 lbs.	25
MSW75T30-CR6	Custom length stainless steel strapping, AISI 316 stainless steel	100-ft. L x 0.75"W x 0.030"T	-/1"	2400 lbs.	1 Roll
MSBW75-C6	Individual buckles use with custom length strapping, AISI 316 (0.75" width)	1.31"L x 1.64"W x 0.070"T	-/1"	-	100

\*Other lengths available, contact Panduit Customer Service.




### Hand Operated Installation Tool for MS Series Strapping

- Screw drive tension mechanism provides high tension with minimal effort, reducing operator fatigue
- Heavy duty construction offers a longer service life
- Allows quick side entry of the strap into tool to speed installation
- For use with 0.75" width strapping only
- Screwdriver required for buckle closure (not included)



### Pre-Printed Wire Marker Books


- Convenient, pocket-sized book
- Full size markers are perforated and can be torn into half size markers for both ends of conductors
- Terminal block markers are included to properly identify connectors
- Ten pages of markers per book
- Pre-printed black on white vinyl-cloth, adhesive back markers
- Temperature Range: -50° to 170°F
- Marker sizes:
  - Full size marker – 0.22" x 1.38". Maximum wire O.D., 0.38"
  - Half size marker – 0.22" x 0.69". Maximum wire O.D., 0.19"
  - Terminal block marker – 0.22" x 0.25"
- Indoor/outdoor rated conformable label can be removed and reused
- Durable, temperature-resistant, and dimensionally stable for rough, textured surfaces
- Resists oil and abrasions



Part No.	Markers	Total Markers Each Legend
PCMB-1	0 thru 9	45
PCMB-2	A thru Z, 0 thru 15, +, -, /	10
PCMB-3	1 thru 45	10
PCMB-4	1, 2, 3	150
PCMB-5	A, B, C	150
PCMB-6	T1, T2, T3	150
PCMB-7	L1, L2, L3	150
PCMB-8	1 thru 15	6
	16 thru 90	4
	A thru Z, +, -, /, 0	2
PCMB-12	A thru Z	15
	+	8
	-	7
	Blank (write-on)	21
PCMB-13	+, -, AC, DC	45
	POS, NEG, GND	21
	NEUT	21
	SPARE, Blank (write-on)	21
PCMB-16	0 thru 33, A, B, C, +, -, L1, L2, L3, T1, T2, T3	10
PCMB-25	0 thru 9	45
	L1, L2, L3, T1, T2, T3	15

### Pre-Printed Wire/Cable Marker Tape Dispenser

- Flexible polyester marker tape conforms tightly to wires/cables
- Dispenser allows marker tape to be cut to the exact length required for marking any size wire/cable
- Durable plastic dispenser can be attached to tool belt for industrial use
- Character height is 0.11"
- Pre-printed black on white, adhesive-back polyester
- Indoor/outdoor rated is resistant to UV light, chemicals, and abrasions
- Excellent long lasting adhesion properties
- Temperature Range: -40° to 250°F



Part No.	Description
PMD-0-9	Dispenser filled with one 8-ft. roll each number 0 thru 9
PMDR-0-9	Replacement refill rolls set for PMD-0-9, one 8-ft. roll each number 0 thru 9

**Blank Self-Laminating Write-On Wire/Cable Marker Books**

- 10 pages of markers per book
- Clear section of marker overlaminates and protects printed legend
- Markers have ink receptive area to allow handwritten legends

Part No.	Marker Size	Markers Per Page	Markers Per Book
PSCB-3Y	1"W x 3"L	6	60
PSCB-6Y	1"W x 6"L	3	30



**Blank Self-Laminating Wire/Cable Marker Dispensers**

- Self-laminating labels are provided in handy dispenser which protects markers when not in use
- Clear section of marker overlaminates and protects write-on legend
- Quick, easy to use for smaller installations and maintenance
- White, adhesive back write-on vinyl
- Indoor/outdoor rated conformable material for general wire/cable labeling
- Temperature Range: -40° to 150°F



Kit Part No.	Refill Roll Part No.	Kit Content	Marker Size	Print-On Height	Min. Cable O.D.	Max. Cable O.D.	Std. Pkg. Qty.
S100X125VARY	S100X125VAFY	(1) Dispenser (1) Roll, white write-on, vinyl label (1) PFX-0 pen	1"W x 1.25"L	0.38"	0.12"	0.28"	Roll of 200
S100X225VARY	S100X225VAFY	(1) Dispenser (1) Roll, white write-on, vinyl label (1) PFX-0 pen	1"W x 2.25"L	0.75"	0.24"	0.48"	Roll of 100