



## CLT50F-C20 Loom Tubing, Black, PE, 0.5" Nom Dia., 100', PK1

CLT50F-C20

The CLT50F-C20 Polyethylene Corrugated Loom Tubing protects cables from impact and abrasion. Features a slit for easy installation onto a bundle of wires or a pre-assembled harness assembly, increasing productivity. Hold in place with cable ties and accessories. Suitable for indoor applications. UL94-HB flammability rating and a maximum temperature rating of 122°F (50°C). Polyethylene. Inside diameter 0.51" (13 mm). Color Black. 1 per package.

### Specifications

Application	Covers wire and cable to protect from abrasion
Note	Slit Wall
Product Type	Corrugated Loom Tubing
Color	Black
Environment	Indoor
Flammability Rating	UL94-HB
Inside Diameter (In.)	0.518
Inside Diameter (mm)	13.16
Material	Polyethylene
Resistance Properties	Impact-Resistant
Maximum Operating Temperature (°C)	50
Minimum Operating Temperature (°C)	-40
Maximum Operating Temperature (°F)	122
Minimum Operating Temperature (°F)	-40
Nominal Diameter (In.)	0.5
Nominal Diameter (mm)	12.7
Outer Diameter (In.)	0.675
Outer Diameter (mm)	17.15
Overall Length (ft.)	100
Overall Length (m)	30.5
Standards Met	RoHS Compliant
Part Features	Provides protection for cables. Slitted for easier install onto a bundle of wires or a pre-assembled harness assembly

**Packaging Detail**

UPC	07498328712
Std. Pkg. Qty.	1
Std. Pkg. Volume (cf)	0.8359
Std. Ctn. Qty.	0
Std. Ctn. Volume (cf)	0.0000