


Panduit Push Button Mount


- UL 62275 Tpe 2,21 per UL file
- Requires no adhesive or additional mounting hardware
- Designed for use where both sides of the panel are accessible




Part Number	Compatible Cross-Section Cable Ties	Pkg Qty	Max Panel Thickness In. (mm)	Panel Hole Diameter In. (mm)	Material	Color	Suitable Environment
PBMS-H25-M	M, I, S	1000	.12 (3.2)	.25 (6.4)	Nylon 6.6	Natural	Indoor

 Panduit Push Barb Cable Tie Mount

- UL 62275 Type 1, 11 per UL file E136577
- Requires no adhesive or additional mounting hardware
- Wing provides added stability
- Can be use where only one side of the panel is accessible




Part Number	Compatible Cross-Section Cable Ties	Package Qty	Max Panel Thickness In. (mm)	Panel Hole Diameter In. (mm)	Material	Color	Suitable Environment
PWMS-H25-M	M, I, S	1000	.11 (2.7)	.25 (6.5)	Nylon 6.6	Natural	Indoor



**Like what you see...
and want more?**

Visit www.panduit.com for the full offering of Panduit products

Panduit Super-Grip™ Adhesive Backed Cable Tie Mounts




- For use with Super-Grip™ Cable Ties
- Low profile design keeps bundle close to mounting surface
- Small overall size allows use where space is limited
- Continuous use temperature for high bond acrylic adhesive is -31°F (-35°C) to 200°F (93°C)
- Produced 2-up for fast and easy liner removal for speed of installation

Part Number	L x W In. (mm)	Depth (including adh.) In. (mm)	Compatible Cross- Section Cable Ties	Pkg Qty	Material	Color	Adhesive Base	Suitable Environment	Static Load Capacity lbs (g)
SGABM20-AV-C300	0.75 x 0.75 (19.1 x 19.1)	.20 (4.9)	M, I, SG100M, SG150I	100	Heat Stabilized Weather Resistant Nylon 6.6	Black	High Bond Acrylic	Outdoor	.56 (254)
SGABM25-AV-C300	1.00 x 1.00 (25.4 x 25.4)	.24 (6.1)	M, I, S, SG100M, SG150I, SG200S, SG250S, SG300S, SG370S	100	Heat Stabilized Weather Resistant Nylon 6.6	Black	High Bond Acrylic	Outdoor	1.0 (453)
SGABM30-AV-C300	1.12 x 1.12 (28.6 x 28.6)	.30 (7.5)	M, I, S, SG100M, SG150I, SG200S, SG250S, SG300S, SG370S	100	Heat Stabilized Weather Resistant Nylon 6.6	Black	High Bond Acrylic	Outdoor	1.2 (567)

Panduit 4-Way Tie Anchor Mounts – Screw Applied

- UL 62275 Type 2, 21 per UL file E136577
- 4-way cable tie entry makes part orientation fast and easy
- Small overall size allows use where space is limited




Part Number	Compatible Cross-Section Cable Ties	Package Qty	Material	Color	Screw Size	Suitable Environment
TA1S8-M	M, I, S	1000	Nylon 6.6	Natural	#8 (M4)	Indoor



Panduit Cable Tie Mounts – Screw Applied

- UL 62275 Type 2, 21 per UL file E136577
- Unique cradle design provides maximum stability for the cable bundles
- Low profile design keeps bundle close to mounting surface




Part Number	Compatible Cross-Section Cable Ties	Pkg Qty	Length (A) In. (mm)	Width (B) In. (mm)	Height (C) In. (mm)	Material	Color	Screw Size	Suitable Environment
TM2S8-C	M, I, S	100	.63 (16.0)	.43 (10.8)	.28 (7.0)	Nylon 6.6	Natural	#8 (M4)	Indoor
TM3S10-C	M, I, S, LH	100	.86 (21.9)	.61 (15.5)	.37 (9.4)	Nylon 6.6	Natural	#10 (M5)	Indoor
TM3S10-M	M, I, S, LH	1000	.86 (21.9)	.61 (15.5)	.37 (9.4)	Nylon 6.6	Natural	#10 (M5)	Indoor



Panduit Extra-Heavy Cable Tie Mounts – Screw Applied

- UL 62275 Type 2, 21 per UL file E136577
- Unique cradle design provides maximum stability for the cable bundles
- Route and support large diameter and heavy cable bundles
- Can also be used with Tak-Ty™ Hook & Loop ties



Part Number	Compatible Cross-Section Cable Ties	Package Qty	Material	Color	Screw Size	Suitable Environment
TMEH-S10-C0	M, I, S, HS, LH, H, EH	100	Weather Resistant Nylon 6.6	Black	#10 (M5)	Outdoor
TMEH-S25-C0	M, I, S, HS, LH, H, EH	100	Weather Resistant Nylon 6.6	Black	1/4 (M6)	Outdoor