


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| PART NO. | MATERIAL | MARKER SIZE inches [mm] | LABELS PER ROW | STANDARD PKG. QTY. | COLOR |
|-------------|-----------|---|-------------------|-----------------------|--------|
| C200X100YJT | GM Y2 | 2.000 (50.80) X X 1.000 (25.40) | 1 | 2500 | WHITE |
| C200X100AAT | GM Y4STE | | | | SILVER |
| C200X100FNT | GMPE4-W | | | | WHITE |
| C200X100PBT | GMP4-W | | | | WHITE |
| C200X100YMT | GM Y4-S | | | | SILVER |
| C200X100YPT | GM Y4-HTW | | | | WHITE |
| C200X100YOT | GM Y4-HTW | | | | BLACK |
| C200X100TJT | GMT2-W | | | | WHITE |



NOTES:
1. MILLIMETERS ARE IN [].

CAD FILENAME/LAYERS 100472EN-DC-C10575/04D

PANDUIT CORP. TINLEY PARK, ILLINOIS

CUSTOMER DRAWING
OPTIMUM C200X100**T
THERMAL TRANSFER LABELS

| REV | DATE | BY | CHK | DESCRIPTION | ECN | R | CUST | SUP |
|-----|---------|-----|-----|---|------|---|------|-----|
| 3 | 9/14/10 | RVU | | REMOVED C200X100YKT FROM THE TABLE. | 6126 | R | | |
| 2 | 11/7/08 | RVU | | ADD P/N: C200X100TJT. ADD TOL. +/- .060 ON WIDTH AND HEIGHT. CHG. ON TITLE TOL. AREA. | 5597 | R | | |
| 1 | 5/17/07 | RVU | | ADDED NEW P/N, C200X100PBT, C200X100YKT C200X100YMT, C200X100YPT AND C200X100YOT. | 5001 | R | | |
| 0 | 4/16/07 | RVU | | DRAWING RELEASE. | 4924 | R | | |

| | | | |
|---|---------------------|---|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .12 (.XXX) ± .020 (.XX) ± .06 ANGLES ± | | UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION. | |
| DRAWN BY RVU | MAT'L: SEE TABLE | SCALE NTS | |
| DATE 4/16/07 | | DRAWING NO. C10575 | DWG A SIZE |
| CHK'D | | | |