




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



**FRONT VIEW**  
SHOWN W/O DUSTCAPS

SEE SHEETS 2 THRU 5  
FOR ARTWORK DETAILS

- NOTES:
- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
  - SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
  - PART NUMBERS:
    - SEE SHEET 2 FOR METHOD B, END 1.
    - SEE SHEET 3 FOR METHOD B, END 2.
    - SEE SHEET 4 FOR KEYED METHOD B, END 1.
    - SEE SHEET 5 FOR KEYED METHOD B, END 2.
  - METHOD B CASSETTES COMPLY WITH ANSI/TIA-568-C.0. SEE ANSI/TIA-568-C.0 FOR POLARITY DETAILS AND EXAMPLES OF B BASIC LINKS.
  - MATERIALS:
    - BOX AND LID: PLASTIC
    - ADAPTER: COMPOSITE PLASTIC
  - CASSETTE WEIGHT: 4.16oz [118g]
  - DIMENSIONS IN BRACKETS ARE METRIC.




00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION				10F113AW-DC-24
REV	DATE	BY	CHK	APR	DESCRIPTION				ECN

TITLE		24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2)	
CUSTOMER DRAWING			
ITEM REVISION NAME		10F113AW/01	
DATASET FILE NAME		10F113AW_DC-24/01A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .03 [ .8 ]      .xxx ± .005 [ .127 ]		SEE NOTES	
.xx ± .01 [ .25 ]      ANGLES ± 5 °		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		10F113AW-DC-24	
DRAWN BY	DATE	CHK	SCALE
SAT	11-26-13	YMG	NONE
SHT 1 OF 5		SIZE	
		A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX LC CASSETTE - METHOD B, END 1

PART NUMBER	DESCRIPTION
FC2Z0-24-10B1	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10B1	24 FIBER 50/125um OM4
FC2X0-24-10B1	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-10B1	24 FIBER 50/125um OM3
FC25N-24-10B1	24 FIBER 50/125um OM2
FC26N-24-10B1	24 FIBER 62.5/125um OM1
FC29N-24-10B1	24 FIBER 9/125um OS1/OS2
FC2SA-24-10B1	24 FIBER 50/125um OM4+, SIGNATURE CORE




METHOD B, END 1 - FIBER LAYOUT

						TITLE 24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING						
						ITEM REVISION NAME 10F113AW/01						
						DATASET FILE NAME 10F113AW_DC-24/01A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .03 (.8)      .xxx ± .005 (.127) .xx ± .01 (.25)      ANGLES ± 5°						
						MATERIAL: SEE NOTES SHEET 1						
						DRAWING NUMBER: 10F113AW-DC-24						
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-24						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE	SHT 2 OF 5	SIZE A

24 FIBER DUPLEX LC CASSETTE - METHOD B, END 2

PART NUMBER	DESCRIPTION
FC2Z0-24-10B2	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10B2	24 FIBER 50/125um OM4
FC2X0-24-10B2	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-10B2	24 FIBER 50/125um OM3
FC25N-24-10B2	24 FIBER 50/125um OM2
FC26N-24-10B2	24 FIBER 62.5/125um OM1
FC29N-24-10B2	24 FIBER 9/125um OS1/OS2
FC2SA-24-10B2	24 FIBER 50/125um OM4+, SIGNATURE CORE




METHOD B, END 2 - FIBER LAYOUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:	DRAWING NUMBER:	SIZE	
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-24	24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING	SEE NOTES SHEET 1	10F113AW-DC-24	A	
							ITEM REVISION NAME 10F113AW/01	<b>PANDUIT</b>			
							DATASET FILE NAME 10F113AW_DC-24/01A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				
							.x ± .03 ( .8 )      .xxx ± .005 ( .127 ) .xx ± .01 ( .25 )      ANGLES ± 5 °				
							THIRD ANGLE PROJECTION				
							DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE	SHT 3 OF 5

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX COLORED/KEYED LC CASSETTE - METHOD B, END 1	
PART NUMBER	DESCRIPTION
FC2Z0-24-**B1	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-**B1	24 FIBER 50/125um OM4
FC2X0-24-**B1	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-**B1	24 FIBER 50/125um OM3
FC25N-24-**B1	24 FIBER 50/125um OM2
FC26N-24-**B1	24 FIBER 62.5/125um OM1
FC29N-24-**B1	24 FIBER 9/125um OS1/OS2
FC2SA-24-**B1	24 FIBER 50/125um OM4+, SIGNATURE CORE

\*\* - INDICATES CHARACTERS REPRESENTING KEYED & NON-KEYED LC ADAPTERS WITH RESPECTIVE COLORS.




METHOD B, END 1 - FIBER LAYOUT (COLORED/KEYED)

						TITLE 24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING						
						ITEM REVISION NAME 10F113AW/01						
						DATASET FILE NAME 10F113AW_DC-24/01A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X ± .xxx ± .010 (0.3) .XX ± .03 (0.8) ANGLES ±						
						MATERIAL: SEE NOTES SHEET 1						
00 11-26-13 SAT YMG ALMY RELEASED TO PRODUCTION						10F113AW-DC-24						
						DRAWING NUMBER: 10F113AW-DC-24						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE	SHT 4 OF 5	SIZE A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX COLORED/KEYED LC CASSETTE - METHOD B, END 2	
PART NUMBER	DESCRIPTION
FC2Z0-24-**B2	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-**B2	24 FIBER 50/125um OM4
FC2X0-24-**B2	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-**B2	24 FIBER 50/125um OM3
FC25N-24-**B2	24 FIBER 50/125um OM2
FC26N-24-**B2	24 FIBER 62.5/125um OM1
FC29N-24-**B2	24 FIBER 9/125um OS1/OS2
FC2SA-24-**B2	24 FIBER 50/125um OM4+, SIGNATURE CORE

\*\* - INDICATES CHARACTERS REPRESENTING KEYED & NON-KEYED LC ADAPTERS WITH RESPECTIVE COLORS.



METHOD B, END 2 - FIBER LAYOUT (COLORED/KEYED)

						TITLE 24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING						
						ITEM REVISION NAME 10F113AW/01						
						DATASET FILE NAME 10F113AW_DC-24/01A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X ± .xxx ± .010 (0.3) .XX ± .03 (0.8)      ANGLES ±						
						MATERIAL: SEE NOTES SHEET 1						
00 11-26-13 SAT YMG ALMY RELEASED TO PRODUCTION						10F113AW-DC-24						
						DRAWING NUMBER: 10F113AW-DC-24						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 5 OF 5	SIZE
							SAT	11-26-13	YMG	NONE		A