




Panduit PN10-10R-L Nylon Insulated Ring Terminal

Type PN-R

- The PN10-10R-L Pan-Term® Terminal is a nylon insulated, ring terminal with funnel entry
- The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94 HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600V per UL 486A/B



Part Number	Wire Range	Color Code	Stock Thickness (In.)	Max. Ins. (In.)	Stud Size	Figure Dimensions (In.)			Recommended Installation Tool	Std. Pkg. Qty.**	Std. Ctn. Qty.
						L	W	C			
PN10-10R-L	12 – 10 AWG	Yellow	0.04	0.225	#10	1.06	0.38	0.31	CT-100‡, CT-1550‡, CT-1551‡, CT-2300/ST‡, CT-2500/L‡, UP14ZLW‡	50	500


**Bulk and/or convenience packaging may be available, contact Panduit® Customer Service for additional information.
‡UL and CSA approved tooling/product combinations. For crimping tool information see www.panduit.com.



Panduit PV10-10R-L Vinyl Insulated Ring Terminal

Type PV-R

- The PV10-10R-L Pan-Term® Terminal is a vinyl insulated, ring terminal
- Braze seam protects terminal barrel from splitting during the crimp process
- Internal barrel serrations assure good wire contact and maximum tensile strength
- Barrel insulation provides protection and strain relief when crimped
- UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600V per UL 486A/B



Part Number	Wire Range	Color Code	Stock Thickness (In.)	Max. Ins. (In.)	Stud Size	Figure Dimensions (In.)			Recommended Installation Tool	Std. Pkg. Qty.**	Std. Ctn. Qty.
						L	W	C			
PV10-10R-L	12 – 10 AWG	Yellow	0.04	0.225	#10	1.05	0.31	0.31	CT-100‡, CT-1550‡, CT-1551‡, CT-2300/ST‡, CT-2500/L‡, UP14ZLW‡	50	500


**Bulk and/or convenience packaging may be available, contact Panduit® Customer Service for additional information.
‡UL and CSA approved tooling/product combinations. For crimping tool information see www.panduit.com.



Panduit PV10-10F-L Vinyl Insulated Fork Terminal

Type PV-F

- The PV10-10F-L Pan-Term® Terminal is a vinyl insulated, fork terminal
- Brazed seam protects terminal barrel from splitting during the crimp process
- Internal barrel serrations assure good wire contact and maximum tensile strength.
- Barrel insulation provides protection and strain relief when crimped
- UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600V per UL 486A/B



Part Number	Wire Range	Color Code	Stock Thickness (In.)	Max. Ins. (In.)	Stud Size	Figure Dimensions (In.)			Recommended Installation Tool	Std. Pkg. Qty.**	Std. Ctn. Qty.
						L	W	C			
PV10-10F-L	14 – 10 AWG	Yellow	0.04	0.225	#10	1.04	0.37	0.25	CT-100‡, CT-1550‡, CT-1551‡, CT-2300/ST‡, CT-2500/L‡, UP14ZLW‡	50	500


**Bulk and/or convenience packaging may be available, contact Panduit® Customer Service for additional information.
 ‡UL Listed, cULus Listed, and CSA approved tooling/product combinations. For crimping tool information see www.panduit.com.



Panduit BSN14-C Nylon Insulated Butt Splice


Type BSN

- The BSN14-C Pan-Term® Splice is a nylon insulated butt splice
- Internal wire stop assures proper insertion length for a quality connection
- Brazed seam protects the terminal barrel from splitting during the crimp process
- UL Flammability UL 94 HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600V per UL 486C



Part Number	Wire Range	Color Code	Max. Ins. (In.)	Figure Dimensions (In.)	Recommended Installation Tool	Std. Pkg. Qty.**	Std. Ctn. Qty.
				L			
BSN14-C	16 – 14 AWG	Blue	0.148	1.15	CT-100, CT-1550, CT-1551, CT-2300/ST, CT-2500/L, UP14ZLW	100	1000

**Bulk packaging may be available, contact Panduit® Customer Service for additional information.
 For crimping tool information see www.panduit.com.



Like what you see... and want more?


Visit www.panduit.com for the full offering of Panduit products



Panduit PV10-10RB-2K Vinyl Insulated Ring Terminal

Type PV-RB

- The PV10-10RB-2K Reel Smart™ Terminal is a continuously molded and insulated ring terminal
- The continuously molded design allows for consistent and reliable processing through Panduit applicators
- Internal barrel serrations assure good wire contact and maximum tensile strength
- UL Flammability UL 94V-0, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600V per UL 486A/B
- Funnel Entry for easy wire insertion




Part Number	Wire Range	Color Code	Stock Thickness (In.)	Max Ins. (In.)	Stud Size	Figure Dimensions (In.)			CA9 Series Crimp Die	CA-800/EZ Series Crimp Die	Pieces Per Reel
						L	W	C			
PV10-10RB-2K	12 – 10 AWG	Yellow	0.04	0.225	#10	1.02	0.31	0.31	CD9-3B	CD-800-3	2000



Panduit Female Disconnects, Nylon Fully Insulated

Type DNF-FIB

- The DNF18-250FIB-3K Reel Smart™ Disconnect is a continuously molded and fully insulated female disconnect with a funnel entry
- The continuously molded design allows for consistent and reliable processing through Panduit applicators
- The internal wire stop assures proper wire insertion length into the terminal barrel for a higher quality connection, and the funnel entry allows for faster wire insertion and lower installed cost
- UL Flammability UL 94 HB, maximum insulation temperature 221°F (105°C)
- UL and CSA rated up to 600V per UL 310



Part Number	Wire Range	Color Code	Max Ins. (In.)	Figure Dimensions (In.)			Tab Size		CA9 Series Crimp Die	CA-800/EZ Series Crimp Die	Pieces Per Reel
				L	W	H	In.	mm			
DNF18-250FIB-3K**	22 – 18 AWG	Red	0.136	0.84	0.35	0.22	0.250 x 0.032	6.3 x 0.8	CD9-4A	CD-800-4	3000
DNF14-250FIB-3K	16 – 14 AWG	Blue	0.160	0.84	0.35	0.22	0.250 x 0.032	6.3 x 0.8	CD9-5A	CD-800-5	3000
DNF10-250FIB-2K	12 – 10 AWG	Yellow	0.220	0.96	0.35	0.23	0.250 x 0.032	6.3 x 0.8	CD9-13B	CD-800-13	2000

**UL with 17 AWG wire.