


24 FIBER DUPLEX LC CASSETTE - METHOD B, END 1

PART NUMBER	DESCRIPTION
FC2Z0-24-10B1	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10B1	24 FIBER 50/125um OM4
FC2X0-24-10B1	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-10B1	24 FIBER 50/125um OM3
FC25N-24-10B1	24 FIBER 50/125um OM2
FC26N-24-10B1	24 FIBER 62.5/125um OM1
FC29N-24-10B1	24 FIBER 9/125um OS1/OS2
FC2SA-24-10B1	24 FIBER 50/125um OM4+, SIGNATURE CORE




METHOD B, END 1 - FIBER LAYOUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:	DRAWING NUMBER:	SIZE	
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-24	24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING	SEE NOTES SHEET 1	10F113AW-DC-24	A	
							ITEM REVISION NAME 10F113AW/01	PANDUIT			
							DATASET FILE NAME 10F113AW_DC-24/01A				
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)				
							.x ± .03 (.8) .xxx ± .005 (.127)				
							.xx ± .01 (.25) ANGLES ± 5°				
								THIRD ANGLE PROJECTION			
							DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE	SHT 2 OF 5

24 FIBER DUPLEX LC CASSETTE - METHOD B, END 2

PART NUMBER	DESCRIPTION
FC2Z0-24-10B2	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-10B2	24 FIBER 50/125um OM4
FC2X0-24-10B2	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-10B2	24 FIBER 50/125um OM3
FC25N-24-10B2	24 FIBER 50/125um OM2
FC26N-24-10B2	24 FIBER 62.5/125um OM1
FC29N-24-10B2	24 FIBER 9/125um OS1/OS2
FC2SA-24-10B2	24 FIBER 50/125um OM4+, SIGNATURE CORE




METHOD B, END 2 - FIBER LAYOUT

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	ITEM REVISION NAME	DATASET FILE NAME	MATERIAL:	DRAWING NUMBER:	
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-24	24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING	10F113AW/01	10F113AW_DC-24/01A	SEE NOTES SHEET 1	10F113AW-DC-24	
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		THIRD ANGLE PROJECTION			
							.x ± .03 (.8) .xxx ± .005 (.127) .xx ± .01 (.25) ANGLES ± 5 °					
							DRAWN BY SAT		DATE 11-26-13		CHK YMG	
							SCALE NONE		SHT 3 OF 5		SIZE A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX COLORED/KEYED LC CASSETTE - METHOD B, END 2	
PART NUMBER	DESCRIPTION
FC2Z0-24-**B2	24 FIBER 50/125um OM4 OPTIMIZED
FC2ZN-24-**B2	24 FIBER 50/125um OM4
FC2X0-24-**B2	24 FIBER 50/125um OM3 OPTIMIZED
FC2XN-24-**B2	24 FIBER 50/125um OM3
FC25N-24-**B2	24 FIBER 50/125um OM2
FC26N-24-**B2	24 FIBER 62.5/125um OM1
FC29N-24-**B2	24 FIBER 9/125um OS1/OS2
FC2SA-24-**B2	24 FIBER 50/125um OM4+, SIGNATURE CORE

** - INDICATES CHARACTERS REPRESENTING KEYED & NON-KEYED LC ADAPTERS WITH RESPECTIVE COLORS.



METHOD B, END 2 - FIBER LAYOUT (COLORED/KEYED)

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	TITLE	MATERIAL:	DRAWING NUMBER:	SIZE
00	11-26-13	SAT	YMG	ALMY	RELEASED TO PRODUCTION	10F113AW-DC-24	24 FIBER DUPLEX LC CASSETTES METHOD B, (ENDS B1 AND B2) CUSTOMER DRAWING	SEE NOTES SHEET 1	10F113AW-DC-24	A
							ITEM REVISION NAME 10F113AW/01	PANDUIT		
							DATASET FILE NAME 10F113AW_DC-24/01A			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .X ± .xxx ± .010 (0.3) .XX ± .03 (0.8) ANGLES ±			
							THIRD ANGLE PROJECTION			
							DRAWN BY SAT	DATE 11-26-13	CHK YMG	SCALE NONE
									SHT 5 OF 5	