



Which Terminal is Right for My Application?

From a trusted brand, Panduit's reputation for exceptional quality products provides solutions for a wide range of applications that will stay strong and outlast the competition. Panduit offers a comprehensive selection of terminal solutions: Premium grade offering which is designed to accommodate a variety of industry requirements suitable for OEM and demanding MRO environments. For contractors looking for an economical solution to satisfy general purpose applications, Panduit® StrongHold™ line will meet this need with a comprehensive assortment of terminals.

StrongHold™ (Contractor Grade)

Pan-Term® (Premium Grade)



Application Environments

224+ Part Numbers

- Suitable for general purpose, light commercial, contractor, residential and HVAC Applications

2000+ Part Numbers

- Highly engineered for OEM / high volume installation applications
- Specifiable for industrial and harsh environment applications
- Wide range of tooling options available from; Manual, Controlled Cycle, Battery Powered, Pneumatic, Semi-Automatic, to Fully Automated Systems



Product Offering

Materials/Environment:

Non-Insulated
Vinyl Insulated
Nylon Insulated

Materials/Environment:

Vinyl Insulated
Premium Nylon
High Temperature
Heat Shrink

Product Offering:

Loose Piece Terminals
Rings
Forks
Disconnects, Bullet Disconnects
Splices, Step-down Splices, Quick Splices
Pins
Joints

Product Offering:

Loose Piece & Reel Feed Terminals
Rings - Standard, Heavy Duty, Tubular
Forks - Standard, Locking, Locking Short, Flanged, Short
Disconnects - Female, Male, Piggyback, Right Angle, Adapter
Splices - Butted, Parallel
Pins
Blades
Joints
Ferrules

Wire Range: 22AWG – 6AWG

Wire Range: 26AWG – 400kcmil*

Stud Sizes: #1/4" - #10

Stud Sizes: #1/4" - #10

Disconnect Tab Sizes:

.187 x .020
.187 x .032
.250 x .032

Disconnect Tab Sizes:

.110 x .032 .187 x .020
.110 x .020 .187/.205 x .032
.145 x .032 .187/.205 x .020
.187 x .032 .250 x .032

Various Standard Packaging Options available starting with 25 and 50 pieces.

Various Standard and Bulk Packaging options starting from 5 pieces to 3,000 pieces on a Reel.**



Compliance Ratings

Applicable sizes are UL Listed and or cULus where applicable, and RoHS Compliant

Applicable sizes are UL Listed and CSA Certified, RoHS compliant, ABS (American Bureau of Shipping) Approved, Class IE Nuclear Rated, DFARS 252.225.7014 Compliant and meet Dept. of Defense Military Specifications MS25036 and MS20659 as noted



Project Based Pricing

—



Application Support

—



Pricing

Value Price Model

Standard Price Model