

Still Using a PDU That's Stuck in the Past?

Upgrade to Smart, Scalable Power with ES2P

Reliable. Intelligent. Just Right.

The ES2P PDU gives you everything you need, and nothing you don't, to modernize your rack infrastructure without overcomplicating your deployment or your budget.

Daisy Chain Smarter

Link up to 16 PDUs per IP address. 4x more than typical models, for reduced networking costs and easier rack scaling.

Gigabit Connectivity

Outdated PDUs slow down monitoring. ES2P features Gigabit Ethernet for faster performance and seamless third-party integration, including Cisco Nexus Dashboard.

Built for Modern Racks

With +/-2% metering accuracy, 55°C temp rating, and a compact footprint, ES2P handles today's heat, density, and uptime expectations, no problem.

Why Settle for 'Good Enough'?

Your power distribution shouldn't be the weakest link in your infrastructure. ES2P gives you a cost-effective PDU that works smarter, installs faster, and fits your footprint.

Perfect Fit For:

- Edge deployments and branch IT closets
- Mid-sized enterprise data centers
- Rack refresh projects and tech upgrades
- Budget-sensitive infrastructure expansions

**Retire that outdated PDU.
Step into smarter power with Panduit.**

Explore the ES2P series at panduit.com/es2p



Specifications

| Part Number | Region | Form Factor | # of CB's | Apparent Power (kVA) | Input Current (A) per Phase | Input Phase | Input Plug Type | Input Voltage Range (VAC) | Phase Connection | Outlet Count | Outlet Type | |
|---------------------------------|--------------|---------------------|--------------------|----------------------|-----------------------------|-------------|--------------------|---------------------------|-----------------------------|-----------------------------|---------------------------------|---------------------------------|
| BASIC PDU | | | | | | | | | | | | |
| E36B26M | NA/ LATAM | Vertical OU MID | 3 | 8.6 | 30(24) | 3 | NEMA L21-30P 5W | 100- 120/200-240 | 3 Phase Wye, L-L | 36 | (30)C13, (6)C19 | |
| E30B25M | | | | | | | | | 3 Phase Wye, L-N, L-L | 30 | (24)C13, (3)C19, (3)5-20R | |
| E24B15M | | | | | | | | | Single Phase, L-L | 24 | (21)C13, (3)C19 | |
| E22B05M | | | 0 | 1.9 | 20(16) | 1 | NEMA L5-20P 3W | 200-240 | Single Phase, L-N | | (20)C13, (2)C19 | |
| E22B10M | | | | | | | | | Single Phase, L-L | 22 | (20)C13, (2)C19 | |
| E22B09M | | | 2 | 2.9 | 30(24) | 1 | NEMA L5-30P 3W | 100-240 | Single Phase, L-N | | (22)5-20R | |
| E20B16M | | | | | | | | | Single Phase, L-L | 20 | (20)C13 | |
| E18B24M | | | Horizontal 2U | 2 | 2.9 | 30(24) | 3 | NEMA L21-30P 5W | 200-240 | 3 Phase Wye, L-L | 18 | (18)C13 |
| E16B41M | | | | | | | | | | Single Phase, L-N | 16 | (16)5-20R |
| MONITORED INPUT PDU (MI) | | | | | | | | | | | | |
| E38D28M | NA/ LATAM | Vertical OU FULL | 3 | 8.6 | 30(24) | 3 | NEMA L21-30P 5W | 100- 120/200-240 | 3 Phase Wye, L-N, L-L | 38 | (30)C13, (6)C19, (2)5-20R | |
| E36D25M | | | | | | | | | Single Phase, L-N | | (32)C13, (6)C19 | |
| E36D29M | | | | | | | | | 3 Phase Delta, L-L | 36 | (30)C13, (6)C19 | |
| E36D26M | | | 3 | 10 | 50(40) | 1 | CS8365 50A 4W | 200-240 | Single Phase, L-L | | (30)C13, (6)C19 | |
| E36D08M | | | | | | | | | 3 Phase Delta, L-L | | (30)C13, (6)C19 | |
| E30D02M | | | Vertical OU MID | 3 | 8.6 | 30(24) | 3 | NEMA L21-30P 5W | 100- 120/200-240 | 3 Phase Wye, L-N, L-L | 30 | (18)C13, (6)C19, (6)5-20R |
| E24D27M | | | | | | | | | | 3 Phase Delta, L-L | 24 | (18)C13, (6)C19 |
| E24D01M | | | | | | | | | | 3 Phase Wye, L-L | | |
| E24D34M | | | | | | | | | | 3 Phase Delta, L-L | | (12)C13, (12)C19 |

More models available at panduit.com