

**Technical Data Sheet****Panduit Raised Panel Label**

This specification is intended to outline the physical and chemical properties of *PANDUIT*'s GMH3-A material and include the following printable material identifiers:

Printable Material Suffixes		
AQT	A0T	
A8T	AMT	
AST	AUT	
AWT	*-30-ES	

**PRODUCT SPECIFICATIONS:**

Description:	Material is RoHS compliant (European Union directive 2002/95/EC). GMH3-A consists of a polyester film laminated to a microcellular foam backed high tack adhesive.
Print Methods:	This material is recommended for thermal transfer printing.
Standard Colors:	Blue, black, yellow, green, red, silver and orange.
Thickness:	27 - 32 mils (ASTM D3652)
Recommended Ribbons:	RMR4BL-A, RMR4WH
Service Temperature Range:	-40°F to 212°F (-40°C to 100°C)
Minimum Application Temperature:	50°F (10°C)
Storage Conditions:	Store at 70°F (21°C) and 50% Relative Humidity.

**PROPERTIES:**

## Peel Adhesion to:

-Stainless Steel

100 oz/in (PSTC-101, 20 min dwell)

150 oz/in (PSTC-101, 24 hour dwell)

-Smooth ABS

100 oz/in (PSTC-101, 20 min dwell)

150 oz/in (PSTC-101, 24 hour dwell)

-Powdercoated surface

100 oz/in (PSTC-101, 20 min dwell)

150 oz/in (PSTC-101, 24 hour dwell)

-Polycarbonate

Tears (PSTC-101, 20 min dwell)

Tears (PSTC-101, 24 hour dwell)

Shear Test

24+ hours (PSTC-107)

Tack

72.0 oz/in (PSTC-16)

**PERFORMANCE:**

Samples were thermal transfer printed with RMR4BL-A, RMER\*BL black resin ribbon and RMR\*WH, RMER\*WH white resin ribbon on the Panduit TDP43MY AND TDP43ME printer. Thermal transfer printed samples were tested as follows:

UV Resistance:

12000 hours\* no change observed (ASTM G154)

Humidity Resistance:

1000 hours at 100F(37C) and 95% R.H, no visible change observed

**Technical Data Sheet**

\*Test conducted in the QUV Weatherometer to assimilate 20 years of expected outdoor exposure under normal conditions.

Long Term High Service Temperature: 1000 hours at 212F(100C), no visible change observed  
 Long Term Low Service Temperature: 1000 hours at -40F(-40C), no visible change observed  
 Abrasion Resistance: Taber abraser, CS-10 wheels/500 gm wt/175 cycles, no visible change observed (ASTM D3389).

**PROPERTIES FOR SOLAR APPLICATION:****PERFORMANCE:**

Short term low temperature exposure: 30 days at -51C, no visible change observed  
 Relative Lightfastness and weatherability: 1000 hours, no change observed (ASTM D3424, Method 4)  
 Tensile Strength: MD: 3985 PSI (ASTM D3759)  
 Elongation: MD: 150% (ASTM D3759)  
 Tack: 9.2N (ASTM D2979)  
 Flammability: 230 seconds (ASTM D1000)  
 Adhesion: 44.7 oz/in (ASTM D3330)

**CHEMICAL/SOLVENT RESISTANCE: Thermal Transfer Print with Black Ribbon**

The testing was conducted at room temperature. Samples were thermal transfer printed with RMR4BL-A, RMER\*BL black resin ribbon on the Panduit TDP43MY AND TDP43ME printer. Separate sets were conditioned for 24 hours before being immersed in the following solvents. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical reagent followed by a 30 minute recovery period. After final immersion, samples were rubbed 10 times with a cotton swab saturated with the test fluid. Visual observations were noted for any smear or loss of legibility.

Chemical/Solvent	Visual Observation of Print without rub	Visual Observation of print with rub
Isopropyl alcohol	No change	No change
Methyl Ethyl Ketone	No change	Loss of print legibility
Alcohol mix*	No change	No change
Gasoline	No change	No change
Diesel	No change	No change
Skydrol	No change	No change
Mil 5606 oil	No change	No change
1,1,1-Trichloroethane	No change	No change
5% Sodium Hydroxide	No change	No change
10% Sulfuric acid solution	No change	No change
Deionized water	No change	No change
10% Salt water solution	No change	No change
n-Hexane	No change	No change
Iso-octane	No change	No change
Ethanol	No change	No change
ASTM#3 oil	No change	No change
Acetone	No change	No change
Bleach	No change	No change

**Technical Data Sheet**


---

\*Alcohol mix is 50% ethanol, 30% methanol, and 20% water by volume.

---

MIL-STD-202G, Method 215K, Solution A, C and D:

3 cycles of three minute immersions in specified fluids followed by toothbrush rub after each immersion. Print remains legible in all three fluids.

**CHEMICAL/SOLVENT RESISTANCE – Thermal Transfer Print with White Ribbon**

The testing was conducted at room temperature. Samples were thermal transfer printed with RMR\*WH, RMER\*WH white resin ribbon on the Panduit TDP43MY and TDP43ME printer. Separate sets were conditioned for 24 hours before being immersed in the following solvents. Testing consisted of 5 cycles of 10 minute immersions in the specified chemical reagent followed by a 30 minute recovery period. After final immersion, samples were rubbed 10 times with a cotton swab saturated with the test fluid. Visual observations were noted for any smear or loss of legibility.

Chemical/Solvent	Visual Observation of Print without rub	Visual Observation of print with rub
Isopropyl alcohol	No change	No change
Methyl Ethyl Ketone	Loss of print legibility	Loss of print legibility
Alcohol mix*	No change	Loss of print legibility
Gasoline	No change	No change
Diesel	No change	No change
Skydrol	No change	Loss of print legibility
Mil 5606 oil	No change	No change
1,1,1-Trichloroethane	No change	Loss of print legibility
5% Sodium Hydroxide	No change	No change
10% Sulfuric acid solution	No change	No change
Deionized water	No change	No change
10% Salt water solution	No change	No change
n-Hexane	No change	No change
Iso-octane	No change	No change
Ethanol	No change	Loss of print legibility
ASTM#3 oil	No change	No change
Acetone	Loss of print legibility	Loss of print legibility

\*Alcohol mix is 50% ethanol, 30% methanol, and 20% water by volume.

---

MIL-STD-202G, Method 215K, Solution A, C and D:

3 cycles of three minute immersions in specified fluids followed by toothbrush rub after each immersion. Print remains legible in solution D but is illegible in solutions A and C.

**PROPERTIES FOR HARSH WASHDOWN ENVIRONMENT**

Meets the requirements of Ingress protection rating standard DIN 40050-9, IP69K and UL50E, Type 4 enclosures for labels used in harsh wash-down and high pressure spray applications, common to the food and beverage industries.

**Technical Data Sheet****CHEMICAL RESISTANCE TEST:**

Samples were printed with RMER4BL and RMER4WH ribbons on Panduit TDP43ME printer. These samples were adhered to stainless steel panels and immersed in the following solvents. Testing consisted of 10 cycles of 10 minutes immersion followed by a 20 minute recovery period. After final immersion, visual observations were noted for any smear or loss of legibility.

CHEMICAL/SOLVENT	TEMPERATURE	PRINT		ADHESIVE
		RMER4BL	RMER4WH	
Enforce LP	50°C	No change	Loss of print legibility	No change
HD PL-10 Plus	RT	No change	No change	No change
Heavy Duty Acid LC-30	70°C	No change	No change	No change
Soil Off II	50°C	No change	Loss of print legibility	No change
Madisan 75	RT	No change	No change	No change
Vortexx	50°C	No change	Loss of print legibility	No change
XY-12	RT	No change	No change	No change

## Approvals:

UL Recognized: UL969

CUL Recognized: C22.2 No. 0.15-01

UL Recognized: UL50E

File Number: MH14979

File Number: MH14979

File Number: MH62615

**LIMITED WARRANTY**

All *PANDUIT* Identification Solution Products (except for Software programs) are warranted to be free from defects in material and workmanship at the time of sale but our obligation under this warranty is limited to replacement of the product proved to be defective within 6 months from the date of sale, or in the case of printers, within 90 days from the date of sale. This warranty is void if the products or printers are modified, altered or misused in any way. Use of *PANDUIT* printers with any product other than the specified *PANDUIT* products for which the printer was designed constitutes misuse. Before using, the user shall determine the suitability of the product for its intended use and user assumes all risk and liability whatsoever in connection therewith. The foregoing may not be altered except by an agreement signed by officers or seller and manufacturer.

NEITHER *PANDUIT* OR SELLER SHALL BE LIABLE FOR ANY OTHER INJURY, LOSS OR DAMAGE, WHETHER DIRECT OR CONSEQUENTIAL, ARISING OUT OF THE USE OF, OR THE INABILITY TO USE THE PRODUCT OR THE PRINTER.

THIS WARRANTY IS MADE IN LIEU OF AND EXCLUDES ALL OTHER WARRANTIES, EXPRESS OR IMPLIED. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS OF PARTICULAR USE ARE SPECIFICALLY EXCLUDED.

The information contained in this literature is based on our experience to date and is believed to be reliable. It is intended as a guide or use by persons having technical skill at their own discretion and risk. We do not guarantee favorable results or assume any liability in connection with its use. Dimensions contained herein are for reference purposes only. This publication is not to be taken as a license to operate under, or a recommendation to infringe any existing patents. This supersedes and voids all previous literature, etc.