

### UL LISTED SF Mini-Com® In-Wall Fiber Spool

- Maintains 1" internal bend radius
- Cable entry/exit from rear, top, and bottom helps maintain external bend radius
- Designed for use with single or double gang wall board adapter

- Stores up to 12 meters of unjacketed fiber cable or two meters of jacketed fiber cable
- 3.65" (92.7mm) depth from rear of faceplate, not for use with in-wall boxes or in shallow walls




Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
<b>CFS2IW</b>	In-wall fiber spool for use with Mini-Com® Faceplates, Faceplate Frames, Inserts and Modular Patch Panels.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).

**Standards: TIA/EIA-568-B requires a minimum 1 meter slack and a fiber spool for in-wall installations.**

### UL LISTED SF Mini-Com® "GFCI" Decora Module Frames

- Mount behind any standard GFCI electrical faceplate
- Accept Mini-Com® Modules for STP and UTP, fiber optic, and audio/video, which snap in and out for easy moves, adds, and changes
- Optional adhesive labels available



CFG1IW

CFG2IW


Part Number	Part Description	Color‡	Std. Pkg. Qty.	Std. Ctn. Qty.
<b>CFG1IW</b>	Module frame accepts one Mini-Com® Module.	Off White	1	10
<b>CFG2IW</b>	Module frame accepts two Mini-Com® Modules.	Off White	1	10
<b>CFG4IW</b>	Module frame accepts four Mini-Com® Modules.	Off White	1	10

‡For other colors replace suffix IW (Off White) with EI (Electric Ivory), WH (White), IG (International Gray), or BL (Black).  
All frames include mounting screws.



CFG4IW

### Component Labels for Mini-Com® "GFCI" Decora Module Frames



#### Suggested Label Solutions for TIA/EIA-606-A Compliance

Frame Part Number	Laser/Ink Jet Desktop Printer Label	TDP43ME Thermal Transfer Desktop Printer Label	PanTher™ LS8E Hand-Held Printer Label	Cougar™ LS9 Hand-Held Printer Label
CFG1	<b>C061X030FJJ</b>	<b>C061X030YPT</b>	<b>C061X030FJC</b>	<b>T031X000FJC-BK</b>
CFG2				
<b>CFG4</b>	<b>C125X030FJJ</b>	<b>C125X030YPT</b>	<b>C125X030FJC</b>	<b>T031X000FJC-BK</b>

For complete labeling solutions and product information, reference charts on pages O.1 – O.22 of SA-NCCB51.