


technical information

Panduit™ Opti-Core™ Gel-Filled Single Armour Single Jacket (SASJ) Outside Plant (OSP) Cable offers gel-filled water-blocking technology, UV resistance, and high density to provide standards compliance and flexibility for outdoor use. Opti-Core™ SASJ OSP Cable has a single outer jacket and corrugated steel armour to provide superior crush resistance for direct burial applications. Opti-Core™ SASJ OSP Cable is available in singlemode (meets OS2 ITU-T G.652.D standards) OM1 multimode, and bend-insensitive OM2, OM3, and OM4 fibre types. Available in fibre counts from 2 to 24 fibres as a “central loose tube” design. Opti-Core™ Fibre Optic Cable is RoHS compliant.



application

Well suited for installation in ducts and on trays. Excellent for direct burial with proper sand back filling. This cable can be used for LAN and WAN backbones, telecom access lines, fibre to business and fibre to the building drop connections; as well as fibre to the home drop and access connections. With MDPE sheathing, this cable is ideal for outdoor installation. This cable is rodent proof.

standards

ISO 11801 2nd edition
EN 50173-1:2002
IEC 60794-1

construction

Strength members	E-glass yarn
Loose tube	02.8 mm jelly-filled loose tube with 2-16 fibres 03.5 mm jelly-filled loose tube with 24 fibres
Water blocking	The core is water blocked using swellable tape and yarn
Armouring	0.15 mm corrugated steel tape
Outer sheath thickness	1.5mm black MDPE sheath, IEC 60811, IEC 60708

Opti-Core™ Gel-Filled Single Armour Single Jacket Outside Plant Cable - EMEA

mechanical properties

Tensile strength (installation)	E1	1000N
Tensile strength (long-term)	E1	500N
Compressive strength (crush)	E3	2000/N
Impact	E4	10 Nm
Torsion	E7	5 cycles ±1 turn
Kink	E10	The cables do not form a kink when a loop is drawn together to a diameter of 100mm
Temperature range	F1	Shipping/Storage: -40° C to +70° C Installation: : -10° C to +60° C Operation: : -30 °C to +70 °C
Water penetration	F5B	No water leakage after 24 hours

physical properties

Fibre Count	Cable O.D. (mm)	Long-Term Bend Radius (mm)	Installation Bend Radius (mm)	Cable Weight (kg/km)
2	8.5	55	110	75
4	8.5	55	110	75
6	8.5	55	110	75
8	8.5	55	110	75
12	8.5	55	110	75
24	8.5	55	110	80

fibre colour code

Fibre colour code	1 Red	7 Brown	13 Yellow w/mark every 70mm	19 Yellow w/mark every 35mm
	2 Green	8 Violet	14 White w/mark every 70mm	20 White w/mark every 35mm
	3 Blue	9 Turquoise	15 Grey w/mark every 70mm	21 Grey w/mark every 35mm
	4 Yellow	10 Black	16 Turquoise w/mark every 70mm	22 Turquoise w/mark every 35mm
	5 White	11 Orange	17 Orange w/mark every 70mm	23 Orange w/mark every 35mm
	6 Grey	12 Pink	18 Pink w/mark every 70mm	24 Pink w/mark every 35mm

Opti-Core™ Gel-Filled Single Armour Single Jacket Outside Plant Cable - EMEA

ordering information

Example: FPSN512- Fibre, Gel-Filled Single Armour Single Central Jacket Outside Plant Cable, Non-rated, OM2, 12-fibre

Character	1	2	3	4	5	6	7
Example	F	P	S	N	5	1	2

1 and 2 – Fibre Product

FP = Fibre- OM1, OM2, OS1/OS2
FQ = Fibre- OM3, OM4

3 – Cable Construction

S = Gel-Filled single armour
single jacket outside
plant cable

4 – Flame Rating

N = Non-rated

5 – Fibre Type

9 = OS1/OS2 9/125µm
6 = OM1 62.5/125µm
5 = OM2 50/125µm
X = OM3 10G 50/125µm
Z = OM4 10G 50/125µm

6 and 7 – Fibre Count

04 = 4-fibre
06 = 6-fibre
08 = 8-fibre
12 = 12-fibre
24 = 24-fibre

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

©2014 Panduit Corp.
ALL RIGHTS RESERVED.
FBDS14--WW-UKE
2/2014

PANDUIT™