


2

1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- 1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
- 2. DIMENSIONS IN BRACKETS [] ARE ENGLISH.
- 3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.



TECHNICAL SPECIFICATIONS		
MAXIMUM LOSS - MULTIMODE 3.5 dB/KM @ 850nm 1.5 dB/KM @ 1300nm	BEND RADIUS	
	INSTALLATION 13.2cm [5.2"]	LONG TERM 6.6cm [2.6"]
MAXIMUM LOSS - SINGLEMODE .75 dB/KM @ 1310nm .75 dB/KM @ 1550nm	TENSILE LOAD	
	INSTALLATION 660 N [150 lbf]	LONG TERM 165 N [38 lbf]
TEMPERATURE		
INSTALLATION	OPERATION	STORAGE
-10° C TO +60° C 14° F TO +140° F	-20° C TO +70° C -4° F TO +158° F	-40° C TO +70° C -40° F TO +158° F

																TITLE 16, 24 FIBER INDOOR/OUTDOOR CABLE WITH 900um TIGHT BUFFER CUSTOMER DRAWING
																ITEM REVISION NAME M02055KD/00
																DATASET FILE NAME M02055KD_DC/00A
																 PART NO. SEE TABLE
															UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (0.3) .xx ± .03 (0.8) ANGLES ±	
																 THIRD ANGLE PROJECTION DRAWING NUMBER: M02055KD-DC
																DRAWN BY SAT DATE 02-13-14 CHK WMA SCALE NONE SHT 1 OF 2 SIZE A
00	02-13-14	SAT	WMA	TCB	RELEASED TO PRODUCTION											M02055KD-DC
REV	DATE	BY	CHK	APR	DESCRIPTION											ECN

2

1

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	FIBER TYPE	FIBER COUNT	JACKET FLAME RATING
FLKR516	MULTIMODE 50/125 OM2	16	OFNR
FLKL516			LSZH
FLKR524		24	OFNR
FLKL524			LSZH
FLKR616	MULTIMODE 62.5/125 OM1	16	OFNR
FLKL616			LSZH
FLKR624		24	OFNR
FLKL624			LSZH
FLKRX16	MULTIMODE 50/125 OM3	16	OFNR
FLKLX16			LSZH
FLKRX24		24	OFNR
FLKLX24			LSZH
FLKRZ16	MULTIMODE 50/125 OM4	16	OFNR
FLKLZ16			LSZH
FLKRZ24		24	OFNR
FLKLZ24			LSZH
FLKR916	SINGLEMODE 9/125	16	OFNR
FLKL916			LSZH
FLKR924		24	OFNR
FLKL924			LSZH

B

B



A

A

						TITLE 16, 24 FIBER INDOOR/OUTDOOR CABLE WITH 900um TIGHT BUFFER CUSTOMER DRAWING						
						ITEM REVISION NAME M02055KD/00			PANDUIT			
						DATASET FILE NAME M02055KD_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm) .x ± .xxx ± .010 (0.3) .xx ± .03 (0.8) ANGLES ±						
00 02-13-14 SAT WMA TCB RELEASED TO PRODUCTION						M02055KD-DC		PART NO. SEE TABLE				
								DRAWING NUMBER: M02055KD-DC				
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY SAT	DATE 02-13-14	CHK WMA	SCALE NONE	SHT 2 OF 2	SIZE A

2

1