


technical information

Panduit™ Opti-Core™ Indoor/Outdoor All-Dielectric Cable with tight buffered fibres is an integral part of the Panduit end-to-end fibre optic solution, designed to support today's data needs while meeting tomorrow's ever-advancing network requirements. This cable provides a water and moisture resistant outer jacket, high density, and easy installation in transitional aerial and duct applications and entrance facilities. 900µm +/- 50µm tight buffered fibres permit easy connectorization permit. Opti-Core™ Fibre Optic Indoor/Outdoor All-Dielectric Cables (2 to 24 fibres) with tight buffered fibres have a non-subunitized design that surrounds the using glass yarn strength members, providing improved rodent protection- effective in many cases. Cables with greater than 24 fibres feature a sub-unit design that simplifies sub-unit and fibre identification, surrounds the fibre inside sub-units with aramid yarn, provides easy access and routing of the fibres, and increases cable durability using a dielectric central strength member. Sub-units made of thin LSZH sheath in the same colours as the outer sheath, marked with unit numbers 1 through 6. Unit diameter approximately 3.5mm. Opti-Core™ Fibre Optic Indoor/Outdoor Riser (OFNR) Rated All-Dielectric Cable with tight buffered fibres tested is in accordance with Telcordia GR-20, Issue 2, GR-409 and with relevant EIA/TIA-455 series FOTPs for fibre optic cable. Opti-Core™ Fibre Optic Indoor/Outdoor Low Smoke Zero Halogen (LSZH) Rated All-Dielectric Cable with tight buffered fibres meets the IEC 60794-1 standard. All standard RoHS compliant multimode and singlemode cable is available in 2, 4, 6, 8, 12, and 24 fibre counts as a "non-subunitized" design and in 36, 48, 72, and 96 fibre counts as a "sub-unitized" design.



application

Can be used for indoor and outdoor applications including LAN and WAN backbones, backbones in data centers, and routing between telecommunications rooms. The cable is suited for installation in ducts and on trays. Cable features a UV stabilized water and moisture resistant outer jacket.

standards

EN 187 000 IEC 60794-2 IEC 60794-2-20	ISO 11801 2 nd edition EN 50-173-1 EN 501-73-1:2002	EuroClass Eca
---	--	---------------

construction

Central strength member	2-24 fibres: E-Glass rovings 36-96 fibres: FRP rod with LSZH covering
Tight buffer	4-96 fibres: 900µm +/- 50µm
Water blocking	The core is water blocked using swellable tape and yarn
Wrapping	Swellable tape
Sheath	2-24 fibres: 1.1mm blue Fire Bur, Halogen free, flame resistant thermoplastic sheathing compound acc. EN 502-0-2-27, UV stabilized 36-96 fibres: LSHF-FR fire retardant, UV stabilized, EN 50290-2-27

fire ratings

IEC 60332-1-2	Single vertical wire test
IEC 60754-1	No halogens
IEC 60754-2	No acid matters
IEC 61034-2	No dense smoke
IEC 60332-3-24=IEC 332-3C (for 24-96 fibres)	Vertically mounted bunched wires and cables

Opti-Core™ Fibre Optic Indoor/Outdoor All-Dielectric Cable with Tight Buffered Fibres - EMEA

mechanical properties

Tensile strength (long-term)	E11	2 to 12-fibres: 500 N 16-fibres: 1000 N 24-fibres: 1500 N 36-fibres: 1200 N 48-fibres: 1400 N 72-fibres: 1800 N 96-fibres: 2200 N
Tensile strength (installation)	E11	2 to 12-fibres: 1000 N 16-fibres: 1400 N 24-fibres: 1600 N 36-fibres: 2400 N 48-fibres: 2800 N 72-fibres: 3600 N 96-fibres: 4400 N
Max. installation load		2 to 12-fibres: 1500 N 16-fibres: 2100 N 24-fibres: 2400 N 36-fibres: 3600 N 48-fibres: 4200 N 72-fibres: 5400 N 96-fibres: 6600 N
Compressive strength (crush)	E3	3000 N/100mm
Impact	E4	20 J
Torsion	E7	5 cycles ±1 turn
Kink	E10	No kink at 12 x cable diameter
Temperature range	F1	Installation: -20 °C to +70 °C (2 to 24-fibres) Operation: -20 °C to +70 °C (2 to 24-fibres) Storage: -40 °C to +70 °C (2 to 24-fibres) Installation: -40 °C to +70 °C (36 to 96-fibres) Operation: -40 °C to +70 °C (36 to 96-fibres) Storage: -40 °C to +70 °C (36 to 96-fibres)
Water penetration	F5B	No water leakage after 24 hours

physical properties

Fibre Count	Cable O.D. (mm)	Installation Bend Radius (mm)	Long-Term Bend Radius (mm)	Cable Weight (kg/km)
2	6	100	50	32
4	6.5	100	50	34
6	6.5	100	50	36
8	7.0	100	50	39
12	7.0	130	75	43
24	12	150	150	150
36	12.5	150	150	165
48	14.5	150	150	230
72	20	200	200	375
96	19	200	200	325

Opti-Core™ Fibre Optic Indoor/Outdoor All-Dielectric Cable with Tight Buffered Fibres - EMEA

fibre colour code 2 to 24 fibres

Fibre colour code	1 Red	7 Brown	13 Yellow w/mark every 70mm	19 Yellow w/mark every 35mm
	2 Green	8 Violet	14 White w/mark every 70mm	20 White w/mark every 35mm
	3 Blue	9 Turquoise	15 Grey w/mark every 70mm	21 Grey w/mark every 35mm
	4 Yellow	10 Black	16 Turquoise w/mark every 70mm	22 Turquoise w/mark every 35mm
	5 White	11 Orange	17 Orange w/mark every 70mm	23 Orange w/mark every 35mm
	6 Grey	12 Pink	18 Pink w/mark every 70 mm	24 Pink w/mark every 35mm

fibre sub-unit colour code 36 to 96 fibres

Fibre colour code	1 Red	4 Yellow
	2 Green	5 white
	3 Blue	6 Grey

ordering information

Example: FAKC912-40 - Fibre Indoor/Outdoor Tight Buffered Unarmored, Euroclass rated, OS2, 12-fibre ,

Character	1	2	3	4	5	6	7	2	2	2
Example	F	A	K	C	9	1	2	-	4	0

1 and 2 – Fibre Product

FA = Fibre,

3 – Cable Construction

K = Indoor/Outdoor
Tight Buffered Unarmored

4 – Flame Rating

C - EuroClass Rated

5 – Fibre Type

6 = OM1 62.5/125µm
5 = OM2 50/125µm
9 = OS2 9/125µm
X = OM3 10G 50/125µm
Z = OM4 10G 50/125µm

6 and 7 – Fibre Count

02 = 2-fibre
04 = 4-fibre
06 = 6-fibre
08 = 8-fibre
12 = 12-fibre
24 = 24-fibre
36 = 36-fibre
48 = 48-fibre
72 = 72-fibre
96 = 96-fibre

8 = Dash

9 and 10 – EuroClass Code

40 - Eca

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

© 2017 Panduit Corp.
ALL RIGHTS RESERVED.
FBDS10--WW-UKE
8/2017

PANDUIT™