

technical information

Panduit™ Opti-Core™ Indoor/Outdoor All-Dielectric Cable is an integral part of the Panduit end-to-end fiber optic solution, designed to support today's data needs while meeting tomorrow's ever-advancing network requirements. This cable provides water-blocking, high density, and easy installation in transitional aerial and duct applications and entrance facilities. Opti-Core™ Fiber Optic Indoor/Outdoor Riser (OFNR) Rated All-Dielectric Cable is tested in accordance with Telcordia GR-20, Issue 2, GR-409 and with relevant EIA/TIA-455 series FOTPs for fiber optic cable. Opti-Core™ Fiber Optic Indoor/Outdoor Low Smoke Zero Halogen (LSZH) Rated All-Dielectric Cable meets the IEC 60794-1 standard. Opti-Core™ Fiber Optic Indoor/Outdoor All-Dielectric Cable features the highest quality OM3 laser optimized fiber to support 10 Gb/s applications while maintaining compatibility with legacy 50µm multimode systems. Fiber Optic Indoor/Outdoor All-Dielectric Cable includes 300 OM3 cable for 300 meter reach requirements and 550 OM4 for 550 meter reach requirements. All standard RoHS compliant multimode and singlemode indoor/outdoor cable is available in 2, 4, 6, 8, and 12-fiber counts as a "central loose tube" design and in 24, 36, and 48-fiber counts in a "stranded loose tube" design.



application

Used for aerial duct and duct applications and features a non-metallic construction that eliminates the need to ground or bond.

standards

Telcordia GR-20 Issue 2
GR-409
EIA/TIA-455

IEC 60794-1
FOTPs series

construction

Central strength member (48 and 72 fiber cables)	Fiberglass Reinforced Plastic (FRP)
Water blocking	4-12-fiber: Water-blocking glass yarn 24-48-fiber: Water-blocking aramid yarn and tape
Outer sheath	LSZH or PVC Riser

Opti-Core™ Fiber Optic Indoor/Outdoor All Dielectric Cable - Asia Pacific

mechanical properties

Tensile strength (<12 fibers)	Installation: 1340 N Long Term: 400 N
Tensile strength (>12 Fibers)	Installation: 2700 N Long Term: 810 N
Compressive strength (crush)	2000 N up to 12 fibers 2200 N greater than 12 fibers
Impact	4.4 Nm
Torsion	100 N, +/- 180°, 10 cycles
Kink	R = 20 x OD (Cable diameter)
Temperature range	Shipping and Storage: -40 °C to +75 °C Installation: -30 °C to +60 °C Operation: -40 °C to +70 °C

physical properties

Fiber Count	Cable O.D. (mm)	Installation Bend Radius (mm)	Long-Term Bend Radius (mm)	Cable Weight (kg/km)
4	8.5	170	85	74(LSZH)/71(Riser)
6	8.5	170	85	74(LSZH)/71(Riser)
8	8.5	170	85	74(LSZH)/71(Riser)
12	8.5	170	85	74(LSZH)/71(Riser)
24	10.8	216	108	113(LSZH)/10(Riser)
48	10.8	216	108	113(LSZH)/10(Riser)

fiber color code

Fiber color code	1 Blue	7 Red
	2 Orange	8 Black
	3 Green	9 Yellow
	4 Brown	10 Violet
	5 Grey	11 Pink
	6 White	12 Aqua

Opti-Core™ Fiber Optic Indoor/Outdoor All Dielectric Cable - Asia Pacific

ordering information

Example: FLCRZ12Y- Fiber, Indoor/Outdoor Unarmored, Central Tube, Riser rated, OM4, 12-Fiber

Character	1	2	3	4	5	6	7	8
Example	F	L	C	R	Z	1	2	Y

1 and 2 – Fiber Product

FL = Fiber OM1, OM2, OS2,
OM3, OM4

3 – Cable Construction

C = I/O Central Tube
(up to 12 fibers)
N = I/O Stranded Tube
(24 fiber & greater)

4 – Flame Rating

R = Riser
L = Low Smoke Zero Halogen

5 – Fiber Type

9 = Singlemode (OS2 ITU G.652.D)
6 = Multimode (OM1)
5 = Multimode (OM2)
X = Multimode (OM3)
Z = Multimode (OM4)

6 and 7 – Fiber Count

04 = 4-Fiber
06 = 6-Fiber
08 = 8-Fiber
12 = 12-Fiber
24 = 24-Fiber
48 = 48-Fiber

8 – RoHS Compliant

Y = Yes

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA
Markham, Ontario
cs-cdn@panduit.com
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT™

© 2016 Panduit Corp.
ALL RIGHTS RESERVED.
FBDS20--WW-ENG
8/24/2016