



PANMPO CONNECTOR




NOTES:

1. IDENTIFICATION:
PANMPO TO LC UNIBOOT HARNESS WITH 2mm UPJACKETED BREAKOUT ASSEMBLY.
2. CABLE:
A. REFERENCE PART NUMBER FOR CABLE/GLASS TYPE.
3. TECHNICAL SPECIFICATIONS:
A. REFER TO PART NUMBER FOR OVERALL LENGTH (WHERE M=METERS AND F=FEET).
4. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
5. DIMENSIONS IN BRACKETS ARE METRIC (mm).



PAIR 1 SHORTEST CONFIGURATION SHOWN
(FIBERS 1 AND 12 ARE REVERSED WHEN PAIR 1 IS LONGEST)

LC UNIBOOT CONNECTOR



REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00	09-26-13	SAT	JGD		RELEASED TO PRODUCTION	M02680FU-DC

TITLE		PANMPO TO LC UNIBOOT STAGGERED PAIR HARNESS (HYDRA) CABLE ASSEMBLY	
ITEM REVISION NAME		M02680FU/00	
DATASET FILE NAME		M02680FU_DC/00A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .010 [0.3]	.XXX ± .010 [0.3]	DRAWING NUMBER: M02680FU-DC	
.XX ± .03 [0.8]	ANGLES ±		
THIRD ANGLE PROJECTION		SIZE	
DRAWN BY	DATE	CHK	SCALE
SAT	09-26-13	JGD	NONE
SHT 1 OF 2		B	

