


HSTT4A Heat Shrink 4 Foot Pieces

- Applications include insulating and protecting oversized electrical and electronic components, cables, terminals and connectors
- Flexible tubing with an adhesive inner wall which seals and protects components from moisture and corrosion
- Voltage: 600 V
- Shrink ratio: 4:1
- Flammability: Flame retardant outer wall meets UL 224 VW-1
- Mil Spec: AMS-DTL-23053/4 Class 3
- Temperature range: -67°F to 257°F (-55°C to 125°C)
- For damp locations
- Material: Adhesive lined black cross-linked Polyolefin



| Part Number | Nominal Diameter | | Min. Expanded I.D. | | Max. Recovered I.D. | | Nominal Recovered Wall Thickness | | Length | | Std. Pkg. Qty. |
|----------------|------------------|------|--------------------|------|---------------------|------|----------------------------------|------|--------|-----|----------------|
| | In. | mm | In. | mm | In. | mm | In. | mm | Ft. | m | |
| HSTT4A15-48-Q | 0.158 | 4.0 | 0.158 | 4.0 | 0.039 | 1.0 | 0.043 | 1.10 | 4 | 1.2 | 25 |
| HSTT4A31-48-Q | 0.315 | 8.0 | 0.315 | 8.0 | 0.079 | 2.0 | 0.043 | 1.10 | 4 | 1.2 | 25 |
| HSTT4A47-48-Q | 0.472 | 12.0 | 0.472 | 12.0 | 0.118 | 3.0 | 0.055 | 1.40 | 4 | 1.2 | 25 |
| HSTT4A62-48-5 | 0.630 | 16.0 | 0.630 | 16.0 | 0.158 | 4.0 | 0.070 | 1.80 | 4 | 1.2 | 5 |
| HSTT4A94-48-5 | 0.945 | 24.0 | 0.945 | 24.0 | 0.236 | 6.0 | 0.088 | 2.25 | 4 | 1.2 | 5 |
| HSTT4A125-48-5 | 1.26 | 32.0 | 1.26 | 32.0 | 0.315 | 8.0 | 0.100 | 2.54 | 4 | 1.2 | 5 |
| HSTT4A200-48-5 | 2.05 | 52.0 | 2.05 | 52.0 | 0.512 | 13.0 | 0.100 | 2.54 | 4 | 1.2 | 5 |

HSTTRA Heat Shrink 4 Foot Pieces

- Applications include insulating and protecting wires and cables
- Semi-rigid tubing with an adhesive inner wall seals and protects components from moisture and corrosion
- Voltage rating: 600 V
- Shrink ratio: 2.5:1 Minimum
- Mil Spec: AMS-DTL-23053/4 Class 1
- Temperature range: -67°F to 230°F (-55°C to 110°C)
- For damp locations
- Material: Adhesive lined black cross-linked Polyolefin



| Part Number | Nominal Diameter | | Min. Expanded I.D. | | Max. Recovered I.D. | | Nominal Recovered Wall Thickness | | Std. Pkg. Qty. |
|----------------|------------------|------|--------------------|------|---------------------|------|----------------------------------|-----|----------------|
| | In. | mm | In. | mm | In. | mm | In. | mm | |
| HSTTRA12-48-Q | 0.125 | 3.2 | 0.125 | 3.2 | 0.023 | 0.6 | 0.038 | 1.0 | 25 |
| HSTTRA19-48-Q | 0.187 | 4.8 | 0.187 | 4.8 | 0.060 | 1.5 | 0.043 | 1.1 | 25 |
| HSTTRA25-48-Q | 0.250 | 6.4 | 0.250 | 6.4 | 0.080 | 2.0 | 0.047 | 1.2 | 25 |
| HSTTRA38-48-Q | 0.375 | 9.5 | 0.375 | 9.5 | 0.135 | 3.4 | 0.050 | 1.3 | 25 |
| HSTTRA50-48-5 | 0.500 | 12.7 | 0.500 | 12.7 | 0.195 | 5.0 | 0.055 | 1.5 | 5 |
| HSTTRA75-48-5 | 0.750 | 19.1 | 0.750 | 19.1 | 0.313 | 8.0 | 0.065 | 1.7 | 5 |
| HSTTRA100-48-5 | 1.00 | 25.4 | 1.00 | 25.4 | 0.400 | 10.6 | 0.075 | 1.9 | 5 |

A.
System
Overview

B1.
Cable Ties

B2.
Cable
Accessories

B3.
Stainless
Steel Ties

C1.
Wiring
Duct

C2.
Surface
Raceway

C3.
Abrasion
Protection

C4.
Cable
Management

D1.
Terminals

D2.
Power
Connectors

D3.
Grounding
Connectors

E1.
Labeling
Systems

E2.
Labels

E3.
Pre-Printed
& Write-On
Markers

E4.
Permanent
Identification

E5.
Lockout/
Tagout
& Safety
Solutions

F.
Index