


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)									
IT940	.33 (8)	1.57 (40)	.065 (1.7)	.350 (8.9)	.82 (20.8)	.30 (7.6)	.556 (14.1)	6.8 (173)	124 (552)	LIGHT HEAVY	.61 (277)
IT965	.33 (8)	2.56 (65)	.065 (1.7)	.350 (8.9)	.82 (20.8)	.30 (7.6)	.556 (14.1)	10.1 (257)	124 (552)	LIGHT HEAVY	.87 (394)
IT9100	.33 (8)	3.94 (100)	.065 (1.7)	.350 (8.9)	.82 (20.8)	.30 (7.6)	.556 (14.1)	14.1 (358)	124 (552)	LIGHT HEAVY	1.17 (531)
* IT9115	.33 (8)	4.53 (115)	.065 (1.7)	.350 (8.9)	.82 (20.8)	.30 (7.6)	.556 (14.1)	15.3 (389)	124 (552)	LIGHT HEAVY	1.31 (598)

NOTES:

- *1) SHORT TIP TIE.
- 2) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

PANDUIT CORP. TINLEY PARK, ILLINOIS

IN-LINE CABLE TIES
IT SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± ---- (.XXX) ± .020(1.51)
(.XX) ± .02(1.5) ANGLES ± ----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
C. HARVELL

MAT'L:

SCALE
NONE

DATE
01/04/94

NYLON 6.6

DRAWING NO.

SS-26873

DWG
A
SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
9	6/2/06	MJVE		CHANGED CROSS SECTION FROM "HEAVY" TO "LIGHT HEAVY"	26873	9		
				ADDED "C" DIMENSION FOR HEAD LENGTH CORRECTED MIN BUNDLE DIAMETER				