

**DB**  
**RATED****One-Hole Grounding Lay-In Lug**

- Used for quick installation of a continuous grounding conductor
- UL 467 Listed for grounding and bonding, copper lugs  
UL Listed for direct burial in earth or concrete

- UL Listed for use up to 600 V and temperature rated 90°C
- Wide wire range-taking capability minimizes inventory requirements

**Copper****Tin-Plated Copper****Aluminum**

Part Number	Set Screw Material	Conductor Size Range	Stud Hole Size In.	Hex Key Size In.	Length In.	Width In.	Height In.	Std. Pkg. Qty.
<b>Copper Body</b>								
<b>LICC4-22-C</b>	Stainless Steel	#14 AWG – #4 AWG	0.22	**	1.09	0.39	0.75	100
<b>Tin-Plated Copper Body</b>								
<b>LICC4-22TP-C</b>	Stainless Steel	#14 AWG – #4 AWG	0.22	**	1.09	0.39	0.75	100
<b>Tin-Plated Aluminum Body</b>								
<b>LIAC4-22-C</b>	Stainless Steel	#14 AWG – #4 AWG	0.22	**	1.06	0.39	0.78	100
<b>LIAS1/0-14-L</b>	Zinc Plated Steel	#14 AWG – 1/0 AWG	0.27	**	1.50	0.61	1.10	50
<b>LIAS250-56-Q</b>	Zinc Plated Steel	#6 AWG – 250 kcmil	0.33	1/4	2.20	0.80	1.70	25

\*\*Uses slotted head set screw.

The use of Panduit oxide inhibiting joint compound (CMP) is recommended for pad to conductor connections. Refer to [www.panduit.com](http://www.panduit.com) for more information.