


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	MAX BUNDLE DIA.	PACKAGE QTY	LENGTH "L" ±.3 [7]
MLT2.7WS-LP	2.7" [69]	50	10.2" [259]
MLT4WS-LP	4" [102]	50	14.3" [362]
MLT6WS-LP	6" [152]	50	20.5" [521]
MLT8WS-LP	8" [203]	50	20.8" [679]
MLT4WS-TL	4" [102]	250	14.3" [362]



- NOTES:
1. APPLICATION TOOLS - GS4MT,PPTMT,ST2MT,ST3MT,HTMT
 2. MINIMUM LOOP TENSILE STRENGTH - 200 LBS (890 NEWTONS) WHEN TESTED ON A 3" MANDREL. PART NO. MLT2.7WS-LP TESTED ON A 1 1/2" MANDREL.
 3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
 4. TOLERANCES:
 .XXX = ±.010 [.25] .XX = ±.02 [.5]
 .X = ±.03 [.8] ANGLES = ±2°
 5. MATERIAL: 304 STAINLESS STEEL

FULLY ROUNDED EDGES ALONG STRAP BODY

SECTION A - A
SCALE: 8x

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
10A	3/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01037
09A	1/13	JAMB	RGRO	---	ADDED PART NUMBER MLT4WS-TL TO DRAWING	-----
08A	2/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----

TITLE		WAVE-TY STANDARD SERIES 304 STAINLESS STEEL CUSTOMER DRAWING	
ITEM REVISION NAME		N41124BS/10	
DATASET FILE NAME		N41124BS_DC/10A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL: 304 STAINLESS STEEL	
.x ± .1 [2.54] .xxx ± .005 [.127]		DRAWING NUMBER: N41124BS_DC	
.xx ± .01 [.25] ANGLES ± 5°		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
JAMB	02/12	DPN	2:1
SHT 1 OF 1			SIZE A