

A. System Overview

## Laser/Ink Jet Non-Laminated Labels

- Labels can be printed in both laser/ink jet printers
- Use as a wrap around label or flag style labels for wire/cable labeling

- Available in polyolefin material and supplied on 8.50" x 11.00" sheets
- Panduit labeling software packages include all label formats for quick and easy label production

B1. Cable Ties

B2. Cable Accessories




B3. Stainless Steel Ties

C1. Wiring Duct

C2. Surface Raceway

### Part Number System for Non-Laminated Labels



C3. Abrasion Protection

C4. Cable Management

D1. Terminals

### Material/Print Method Selection Guide

| Material               | Print Method      | Temperature Range              | Features                                                                                       |
|------------------------|-------------------|--------------------------------|------------------------------------------------------------------------------------------------|
| Polyolefin, White (FJ) | Laser/Ink Jet (J) | -40°F to 180°F (-40°C to 82°C) | Indoor/outdoor rated; conformable material for general identification; excellent print quality |

D2. Power Connectors

D3. Grounding Connectors

| Part Number        | Part Description         | Width |      | Length |      | Min. Cable O.D. |      | Max. Cable O.D. |      | Std. Pkg. Qty. | Std. Ctn. Qty. |
|--------------------|--------------------------|-------|------|--------|------|-----------------|------|-----------------|------|----------------|----------------|
|                    |                          | In.   | mm   | In.    | mm   | In.             | mm   | In.             | mm   |                |                |
| <b>N025X075FJJ</b> | White, polyolefin label. | 0.25  | 6.4  | 0.75   | 19.1 | 0.240           | 6.1  | 0.51            | 13.0 | 10000          | 50000          |
| <b>N025X125FJJ</b> | White, polyolefin label. | 0.25  | 6.4  | 1.25   | 31.8 | 0.400           | 10.2 | 0.85            | 22.0 | 10000          | 50000          |
| <b>N025X150FJJ</b> | White, polyolefin label. | 0.25  | 6.4  | 1.50   | 38.1 | 0.48            | 12.2 | 1.02            | 25.9 | 10000          | 50000          |
| <b>N050X075FJJ</b> | White, polyolefin label. | 0.50  | 12.7 | 0.75   | 19.1 | 0.240           | 6.1  | 0.51            | 13.0 | 10000          | 50000          |
| <b>N050X125FJJ</b> | White, polyolefin label. | 0.50  | 12.7 | 1.25   | 31.8 | 0.400           | 10.2 | 0.85            | 21.6 | 10000          | 50000          |
| <b>N050X150FJJ</b> | White, polyolefin label. | 0.50  | 12.7 | 1.50   | 38.1 | 0.48            | 12.2 | 1.02            | 25.9 | 5000           | 25000          |
| <b>N100X075FJJ</b> | White, polyolefin label. | 1.00  | 25.4 | 0.75   | 19.1 | 0.240           | 6.1  | 0.51            | 13.0 | 5000           | 25000          |
| <b>N100X125FJJ</b> | White, polyolefin label. | 1.00  | 25.4 | 1.25   | 31.8 | 0.400           | 10.2 | 0.85            | 22.0 | 5000           | 25000          |
| <b>N100X150FJJ</b> | White, polyolefin label. | 1.00  | 25.4 | 1.50   | 38.1 | 0.48            | 12.2 | 1.02            | 25.9 | 2500           | 10000          |

E1. Labeling Systems

E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/Tagout & Safety Solutions

F. Index

Order number of labels required in multiples of Std. Pkg. Qty.