




PANDUIT P/N	WEIGHT
Q1T1B3H0A24AFA0	X.XXkg (XX.Xlb)

NOTES:

- IDENTIFICATION: VERTICAL, MIXED (18) C13 LOCKING & (6) C19 LOCKING, NETWORK-ENABLED MONITORED WITH MONITORED PER OUTLET, 230V / 16A / SINGLE-PHASE PDU
- ACCESSORY COMPONENTS: (1) QUICK-START GUIDE
- PRIMARY DIMENSIONS ARE IN MILLIMETERS, SECONDARY DIMENSIONS IN [ INCHES ]
- INPUT POWER (AMPS, VOLTS, kWh, kVA, POWER FACTOR, FREQUENCY) MONITORING. DATA CAN BE ACCESSED ON UNIT DISPLAY OR REMOTELY WHEN CONNECTED VIA ETHERNET CONNECTION
- OUTLET LEVEL POWER (AMPS, VOLTS, POWER FACTOR, FREQUENCY) MONITORING CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION
- RoHS COMPLIANT
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART
- MAXIMUM AVAILABLE INPUT POWER = 3.7 kW
- INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES

PART NO.      COLOR  
 Q1T1B3H0A24AFA0      BLACK



PLUG  
16 AMP, 250V  
2P/3W  
IEC 60309, SPLASHPROOF

EIGHTEEN (18)  
LOCKING RECEPTACLES  
10 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13

SIX (6)  
LOCKING RECEPTACLES  
16 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
00A	2-5-15	MRWA	GLM	EDM	RELEASED TO PRODUCTION	12V092CE

WE ASK THAT YOU CHECK FULLY THE DIMENSIONS, NOTES, AND SIGN THE CLIENT SIGNATURE BOX.  
 THE JOB WILL NOT PROGRESS WITHOUT SIGNED APPROVAL. PLEASE DO NOT DELAY IN RETURNING PROOF AS IT WILL AFFECT DELIVERY.

SIGN	DATE	PRINT
------	------	-------

TITLE  
**SMARTZONE NETWORK-ENABLED MPO SERIES RACK PDU**  
 Q1T1B3H0A24AFA0  
 CUSTOMER DRAWING

ITEM REVISION NAME  
 12V092CE/00.PRT

DATASET FILE NAME  
 12V092CE\_DC/00A.PRT

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:  
 INCHES: X.X +/-, X.XX +/-, X.XXX +/-  
 METRIC - MILLIMETER: X +/-, X.X +/-, X.XX +/-  
 ANGLE: +/-

MATERIAL/COLOR:  
 N/A

DRAWING NUMBER:  
 12V092CE\_DC

THIRD ANGLE PROJECTION

DRAWN BY: MRWA, DATE: 2-5-15, CHK: GLM, SCALE: NTS

SHT 1 OF 1, SIZE: B