


## Pan-Ty® Cable Ties – Weather Resistant Nylon 12

- For high moisture, corrosive (zinc chloride and dilute acids), and low temperature indoor or outdoor applications
- Cable tie of choice for making attachments to galvanized surfaces
- One-piece construction for consistent performance and reliability
- Lowest threading force of any one-piece cable tie in the industry
- Curved tip is easy to pick up from flat surfaces and allows faster initial threading to speed installation



| Part Number                                     | Length |     | Width |     | Thickness |     | Max. Bundle Dia. |     | Min. Loop Tensile Str. |     | Recommended Installation Tool                          | Std. Pkg. Qty. | Std. Ctn. Qty. |
|---|--------|-----|-------|-----|-----------|-----|------------------|-----|------------------------|-----|--|----------------|----------------|
|   | In.    | mm  | In.   | mm  | In.       | mm  | In.              | mm  | Lbs.                   | N   |  |                |                |
| <b>Intermediate Cross Section</b>               |        |     |       |     |           |     |                  |     |                        |     |  |                |                |
| <b>PLT1.5I-M120</b>                             | 5.6    | 142 | .142  | 3.6 | .045      | 1.1 | 1.38             | 35  | 25                     | 111 | GTS, GTSL, GS2B, PTS, PPTS, STS2                       | 1000           | 25000          |
| <b>Standard Cross Section</b>                   |        |     |       |     |           |     |                  |     |                        |     |  |                |                |
| <b>PLT2S-M120</b>                               | 7.4    | 188 | .190  | 4.8 | .052      | 1.3 | 1.88             | 48  | 40                     | 178 | GTS, GTSL, GS2B, GTH, GS4H, PTS, PTH, PPTS, STS2, STH2 | 1000           | 10000          |
| <b>PLT4S-M120</b>                               | 14.5   | 368 | .190  | 4.8 | .052      | 1.3 | 4.00             | 102 | 40                     | 178 |  | 1000           | 5000           |
| <b>Light-Heavy Cross Section (Straight Tip)</b> |        |     |       |     |           |     |                  |     |                        |     |  |                |                |
| <b>PLT4H-TL120</b>                              | 14.5   | 368 | .300  | 7.6 | .075      | 1.9 | 4.00             | 102 | 90                     | 400 | GTH, GTSL, GS4H, GS4EH, PTH, STH2, ST3EH               | 250            | 2500           |
| <b>PLT8LH-C120</b>                              | 27.6   | 701 | .300  | 7.6 | .075      | 1.9 | 8.00             | 203 | 90                     | 400 |  | 100            | 2000           |

A.  
System  
Overview

B1.  
Cable Ties

B2.  
Cable  
Accessories

B3.  
Stainless  
Steel Ties

C1.  
Wiring  
Duct

C2.  
Surface  
Raceway

C3.  
Abrasion  
Protection

C4.  
Cable  
Management

D1.  
Terminals

D2.  
Power  
Connectors

D3.  
Grounding  
Connectors

E1.  
Labeling  
Systems

E2.  
Labels

E3.  
Pre-Printed  
& Write-On  
Markers

E4.  
Permanent  
Identification

E5.  
Lockout/  
Tagout  
& Safety  
Solutions

F.  
Index