



3933 US ROUTE 11, CORTLAND, NEW YORK 13045

Phone Number: 1-800-345-3851 Fax Number: 607-758-3648

## REPORT OF TEST

Panduit Corporation  
10500 West 167<sup>th</sup> Street  
Orland Park, IL 60467

*The products described in this Report were tested for compliance to the standard(s) listed below. The products listed below are not part of an Intertek Verification Program and the results are provided to the client as a one time performance test.*

**Reference Intertek Report No.:** 102067265CRT-001d

**Date:** March 31, 2015

**Test:**

Electrical performance testing of a telecommunication patch cords to the requirements of ANSI/TIA-568-C.2 for Category 6A patch cords.

**Standards and sections used:**

ANSI/TIA-568-C.2-2009: Balanced Twisted-Pair Telecommunications Cabling and Components Standards, dated August 2009 (Section 6.9, Cords and Jumpers Transmission Performance)

ANSI/TIA-568-C.2-2-2014: Balanced Twisted-Pair Telecommunications Cabling and Components Standards, Addendum 2: Alternative Test Methodology for Category 6A Patch Cords, dated November 2014 (Section 4, General)

**Sample description:**

The client supplied five (5) samples of 1 meter length category 6A, S/FTP patch cords identified as part number STP6X1MBBL and five (5) samples of 15 meters length category 6A, S/FTP patch cords identified as part number STP6X15MBU. The samples were received on March 30, 2015 and were in good condition.

**Conclusion:**

The telecommunication patch cords, as previously described and supplied by the client, were tested in accordance with the standard referred to above, and did comply with the indicated applicable transmission requirements. The testing was performed at Intertek located in Cortland, New York.

Reviewed and approved by:

John Cash  
Associate Engineer  
Global Cabling Products Testing

Antoine Pelletier  
Project Engineer  
Global Cabling Products Testing

This report is for the exclusive use of Intertek's Client and is provided pursuant to the agreement between Intertek and its Client. Intertek's responsibility and liability are limited to the terms and conditions of the agreement. Intertek assumes no liability to any party, other than to the Client in accordance with the agreement, for any loss, expense or damage occasioned by the use of this report. Only the Client is authorized to copy or distribute this report and then only in its entirety. Any use of the Intertek name or one of its marks for the sale or advertisement of the tested material, product or service must first be approved in writing by Intertek. The observations and test results in this report are relevant only to the sample tested. This report by itself does not imply that the material, product, or service is or has ever been under an Intertek certification program.