

Heavy Duty Mounts and Assemblies

Heavy duty mounts help secure wire, cable and hose bundles making installation more efficient and cost effective. Panduit heavy-duty cable ties and mounts are made of rugged, highly durable materials; ideal for trains, subways, heavy equipment, trucks and buses. The Wide Strap Extra Heavy cable tie has a strong 120 lbs. loop tensile strength to provide secure support for even high load applications.




Key Features	Benefits
Versatile Material	New Nylon 6/6 material is Heat stabilized (115°C), UV weather resistant, and impact modified
Simplifies Assembly Process	Extra Heavy Tie Mounts available pre-assembled with the Pan-Ty® Wide Strap Extra Heavy Cable Ties
Maximized Stability	Unique design allows maximum stability for large diameter and heavy cable bundles

Ordering information

Extra Heavy Tie Mounts and Assemblies with Wide Strap Cable Ties

- Extra-heavy screw applied cable tie mounts
- Available with Pan-Ty Wide Strap Extra Heavy cable ties pre-assembled with mount



Part Number	Used with Cable Ties‡	Material	Color	Environment	Mounting Method	Std. Pkg. Qty.	Std. Ctn. Qty.
TMEH2S5-D350	M, I, S, HS, LH, H, EH	Impact modified heat stabilized weather resistant nylon 6.6	Black	Outdoors or Indoors	#10 (M5) Screw	500	2000
TMEH2S6-D350					1/4 (M6) Screw	500	2000
TMEH2S8-D350					5/16 (M8) Screw	500	2000
TMEH2S5-3E-C350	PLWS3EH-TL350 Wide Strap Cable Tie pre-installed				#10 (M5) Screw	100	1000
TMEH2S6-3E-C350					1/4 (M6) Screw	100	1000
TMEH2S8-3E-C350					5/16 (M8) Screw	100	1000


‡Cable Tie Cross Section: M = Miniature, I = Intermediate, S = Standard, LH = Light-Heavy, H = Heavy, and EH = Extra Heavy

Heavy Duty Mounts and Assemblies

Ordering information

Screw Applied Tie Mounts

- Unique cradle design provides maximum stability for cable bundle
- Route and support large diameter and heavy cable bundles




Part Number	Used with Cable Ties‡	Material	Color	Environment	Mounting Method	Std. Pkg. Qty.	Std. Ctn. Qty.
TMEH-S8-Q0	M, I, S, HS, LH, H, EH	Weather Resistant Nylon 6.6	Black	Outdoors	#8 (M4) Screw	25	250
TMEH-S10-Q0					#10 (M5) Screw	25	250
TMEH-S25-Q0		Weather Resistant Polypropylene			1/4 (M6) Screw	25	250
TMEH-S10-C100					#10 (M5) Screw	100	500
TMEH-S10-C109		Polypropylene	Green	Indoors	#10 (M5) Screw	100	500

‡Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, EH = Extra-Heavy.

Swivel Mounts

- The two mounts are securely fastened together with a connecting rivet that allows both mounts to rotate
- Can join bundles of cable, tubing, or hoses that may need to move or are not parallel
- Separates bundles to avoid abrasion
- Material: Weather Resistant Nylon 6.6



Part Number	Used with Cable Ties‡	Pull Apart Force		Color	Environment	Std. Pkg. Qty.	Std. Ctn. Qty.
		Lbs.	g				
TM3-X2-C0Y	M, I, S, HS, LH	120	54,431	Black	Indoors/Outdoors	100	1000
TMEH-X2-L0Y	M, I, S, HS, LH, H, EH	250	113,398			50	500

‡Cable tie cross section sizes: M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, EH = Extra-Heavy.

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA
Phone: 800.777.3300

PANDUIT EUROPE LTD.
London, UK
cs-emea@panduit.com
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.
Republic of Singapore
cs-ap@panduit.com
Phone: 65.6305.7575

PANDUIT JAPAN
Tokyo, Japan
cs-japan@panduit.com
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA
Guadalajara, Mexico
cs-la@panduit.com
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.
Victoria, Australia
cs-aus@panduit.com
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com
or by phone: 800.777.3300

PANDUIT®

©2017 Panduit Corp.
ALL RIGHTS RESERVED.
CMCB03--SA-ENG
5/2017