

# TX6A-SD™ 10Gig UTP Patch Cords with MaTriX Technology

## specifications

Category 6A/Class E<sub>A</sub>, UTP patch cords shall be constructed of 26 AWG stranded copper cable with an enhanced performance modular plug on each end. Copper conductors in patch cable shall be twisted in pairs and separated by a quadrant separator. All four pairs shall be surrounded by matrix tape and a flame retardant jacket. The patent pending matrix tape shall suppress alien crosstalk and allow 10 Gb/s transmission. Patch cord cable shall be offered in multiple colors and lengths for design flexibility.



## technical information

<b>Category 6A/Class E<sub>A</sub> channel and component performance</b>	Exceeds all ANSI/TIA-568.2-D Category 6A and ISO 11801 Class E <sub>A</sub> standards for all frequencies up to 500 MHz <sup>3</sup>
<b>Attenuation de-rating factor:</b>	1.5
<b>Cable diameter:</b>	0.240 in. (6.1mm) nominal
<b>FCC and ANSI compliance:</b>	Meets ANSI/TIA-1096-A (formerly FCC Part 68); contacts are plated with 50 microinches of gold for superior performance
<b>IEC compliance:</b>	Meets IEC 60603-7
<b>RoHS compliance:</b>	Compliant
<b>Operating temperature:</b>	14°F to 140°F (-10°C to 60°C)
<b>Storage temperature</b>	-40°F to 158°F (-40°C to 70°C)
<b>PoE compliance:</b>	Rated for 2500 cycles with IEEE 802.3af / 802.3at and 802.3bt type 3 and type 4
<b>C(UL)US listed:</b>	UL 1863, CSA standard C22.2
<b>Flammability rating:</b>	CM or LSZH

## key features and benefits

<b>Interoperable</b>	Compatible with components of the TX6A™ 10Gig UTP Copper Cabling System for increased design flexibility in channels up to 100 meters
<b>MaTriX Technology</b>	Provides superior suppression of both PSANEXT and PSAACR-F; improves the installation flexibility by allowing cable combing in existing pathways without compromising performance
<b>Smaller cable diameter than most Category 6 patch cords and flexible cable design</b>	Improved cable routing and management in high density applications enabling easier installations
<b>100% performance tested for wire map, NEXT and return loss</b>	Confidence that each patch cord delivers critical component level performance
<b>Superior headroom warranty</b>	Provides the highest margins above the industry standard for both electrical and alien crosstalk performance
<b>Center de-embedded plug</b>	Performs in center of ANSI/TIA-568.2-D component range ensuring interoperability and superior performance
<b>Integral pair manager</b>	Optimizes performance, consistency, and reliability by reducing untwist at plug
<b>Patented tangle-free latch</b>	Prevents snags and provides easy release, saving time and providing reliability on frequent moves, adds, and changes
<b>Slender strain relief boot</b>	Provides easy access in high-density applications
<b>Robust construction</b>	Rated to 2500 mating cycles
<b>Identification</b>	Provides identification of performance level, length, and quality control number for future traceability
<b>Variety of cable colors and lengths</b>	Meets individual length and color-coding requirements for greater system flexibility
<b>Color bands (optional)</b>	Snap onto cable, allowing additional color-coding options
<b>RJ45 plug lock-in device (optional)</b>	Secures plug into jack to prevent unauthorized removal of patch cord

## applications

The TX6A-SD™ 10Gig UTP Patch Cords is a component of the TX6A-SD™ and TX6A™ 10Gig Copper Cabling Systems with MaTriX Technology. Interoperable and backward compatible, these end-to-end systems provide design flexibility to protect network investments well into the future. Key applications include:

- 10GBASE-T Ethernet
- Data center I/O consolidation
- Data center server virtualization
- Back-bone aggregation
- Parallel processing and high speed computing

### TX6A-SD™ 10Gig UTP Copper Cabling System with MaTriX Technology

#### TX6A-SD™ 10Gig UTP Patch Cords with MaTriX Technology

<b>CM (foot lengths):</b>	UTP6ASD^BU
<b>CM (meter lengths):</b>	UTP6ASD^^MBU
<b>LSZH (meter lengths):</b>	UTP6ASDL^^MBU

#### Tools and Accessories

<b>Patch cord removal tool:</b>	PCRT1
<b>Flashlight kit:</b>	KPCRT1-FL
<b>Patch cord color band:</b>	PCBAND***-Q
<b>Standard RJ45 plug lock-in device:</b>	PSL-DCPLX‡
<b>Recessed RJ45 plug lock-in device:</b>	PSL-DCPLRX‡

<sup>^</sup> For lengths 3 to 20 feet (increments of one foot) 20, 25, 30, 35, or 40 feet change the length designation in part number to the desired length. For standard cable colors other than Off White, add suffix BL (Black), BU (Blue), GR (Green), RD (Red), YL (Yellow), OR (Orange), GY (Gray) or VL (Violet) at the end of the part number. For example, the part number for a blue, 15-foot patch cord is UTP6ASD15BU.


<sup>^^</sup> For lengths 1, 1.5, 2, 2.5, 3, 5, 6, 7 meters, change the length designation in the part number to the desired length. For standard cable colors other than Off White, add suffix BL (Black), BU (Blue), RD (Red), YL (Yellow), GR (Green), OR (Orange), GY (Gray) or VL (Violet). For example, the part number for a blue, 5-meter patch cord is UTP6ASD5MBU.

<sup>\*\*\*</sup> To designate color, add suffix WH (White), EI (Electric Ivory), IG (Int'l Gray), BL (Black), BU (Blue), RD (Red), YL (Yellow), GR (Green), OR (Orange), or VL (Violet) before -Q in part number. 25/package.

<sup>‡</sup> For colors other than Red, add -BL (Black), -BU (Blue), -GR (Green), -YL (Yellow), -OR (Orange), -IW (International White), or -IG (International Gray) to the end of the part number. 10/package. Add -C for bulk packages of 100. Contact customer service for keyed connectivity, bulk packaged jack modules and patch cords.

<sup>◇</sup> Lengths 1m to 15m or 6 inch to 49 feet are guaranteed to meet TIA and ISO component and channel requirements. Lengths greater than 15m or 49 feet are guaranteed to meet ISO component and both TIA and ISO channel requirements.

# TX6A-SD™ 10Gig UTP Patch Cords with MaTriX Technology



**T568B Wiring Scheme**

Plug Position	Cable Wire
1	White/Orange
2	Orange
3	White/Green
4	Blue
5	White/Blue
6	Green
7	White/Brown
8	Brown



## WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA  
Markham, Ontario  
cs-cdn@panduit.com  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
cs-emea@panduit.com  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
cs-ap@panduit.com  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
cs-japan@panduit.com  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
cs-la@panduit.com  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
cs-aus@panduit.com  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

For more information

Visit us at [www.panduit.com](http://www.panduit.com)

Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

**PANDUIT**®

©2018 Panduit Corp.  
ALL RIGHTS RESERVED.  
COSP300--WW-ENG  
Replaces SA-COSP194  
12/2018