


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PRE-INSTALLED SWITCH WIRING

EACH SWITCH CAN HAVE (1) EXPANSION IN A 24" X 24" ENCLOSURE



OOA	3/12/18	JBO	NWW	TIMH	RELEASED TO CUSTOMER	15V510TP
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN


TITLE INTEGRATED NETWORK ZONE SYSTEM, ALLEN-BRADLEY STRATIX 5700, 8000, AND 8300 SWITCHES WITH OPTIONAL EXPANSIONS AND INCLUDED CONNECTIVITY CUSTOMER DRAWING			
ITEM REVISION NAME 15V510TP/00.PRT		PANDUIT TM	
DATASET FILE NAME 15V510TP_DC/00A.PRT		MATERIAL/COLOR: N/A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES +/- 0.03 METRIC - MILLIMETER +/- 0.8 X.X +/- 0.018 X.X +/- 0.46 ANGLE +/- 1° X.XX +/- 0.007 X.XX +/- 0.18			DRAWING NUMBER: 15V510TP
DRAWN BY JBO		DATE 3/12/18	CHK NWW
SCALE 1:8		THIRD ANGLE PROJECTION	
SHT 1 OF 3		SIZE A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	ENCLOSURE TYPE	ALLEN BRADLEY SWITCH	ALLEN BRADLEY COPPER EXPANSION	ALLEN BRADLEY FIBER EXPANSION	NUMBER OF DOWNLINK PATCH CORDS	ALLEN BRADLEY UPLINK TRANSCEIVER	NUMBER OF UPLINK PATCH CORDS
Z22N-SDADO	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z224-SFAA1	4/12 STEEL	(1) 1783-HMS16TG4CGR	N/A	N/A	(16) UTP COPPER	NONE	(2) UTP COPPER
Z22N-SDAA1	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	NONE	(2) UTP COPPER
Z22N-SDAB1	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP100FX	(2) OM3 MM FIBER
Z22N-SDAD1	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SEAD1	4/12 STEEL	(1) 1783-BMS20CGP	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SHAD1	4/12 STEEL	(1) 1783-BMS20CGN	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SBAD4	4/12 STEEL	(1) 1783-MS10T	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SDAB4	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP100FX	(2) OM3 MM FIBER
Z22N-SDAD4	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SEAD4	4/12 STEEL	(1) 1783-BMS20CGP	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SHAD4	4/12 STEEL	(1) 1783-BMS20CGN	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SHAD4GR	4/12 STEEL	(1) 1783-BMS20CGN	N/A	N/A	(16) GREEN UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SIAD4	4/12 STEEL	(1) 1783-BMS10CGN	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER

NOTES:

- CAT 6 UTP COPPER PATCH CORDS AND JACKS, PANDUIT PART NUMBERS (UTP28SP3) AND (CJ688TG1W)
- CAT 6 UTP COPPER PATCH CORDS AND JACKS, PANDUIT PART NUMBERS (UTP28SP3GR) AND (CJ688TGGR)
- MM, OM3 FIBER PATCH CORDS AND ADAPTERS, PANDUIT PART NUMBER (FX2ERLNLNSNM001) AND (CMDSAQLCZBL)
- SFP TRANSCEIVERS, 100 BASE MULTIMODE, ALLEN-BRADLEY PART NUMBER (1783-SFP100FX)
- SFP TRANSCEIVERS, 1 GIG MULTIMODE, ALLEN-BRADLEY PART NUMBER (1783-SFP1GSX)


					TITLE		INTEGRATED NETWORK ZONE SYSTEM, ALLEN-BRADLEY STRATIX 5700, 8000, AND 8300 SWITCHES WITH OPTIONAL EXPANSIONS AND INCLUDED CONNECTIVITY					
					ITEM REVISION NAME		CUSTOMER DRAWING					
					15V510TP/00.PRT		PANDUIT TM					
					DATASET FILE NAME					15V510TP_DC/00A.PRT		
					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:					
					INCHES		METRIC - MILLIMETER		ANGLE			
					X.X +/- 0.03		X.X +/- 0.8		+/- 1°			
					X.XX +/- 0.018		X.X +/- 0.46		N/A			
					X.XXX +/- 0.007		X.XX +/- 0.18		DRAWING NUMBER:			
OOA 3/12/18 JBO NWW TIMH REFER TO SHEET 1					15V510TP		 THIRD ANGLE PROJECTION		15V510TP			
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 2 OF 3	SIZE
							JBO	3/12/18	NWW	1:8		A

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	ENCLOSURE TYPE	ALLEN BRADLEY SWITCH	ALLEN BRADLEY COPPER EXPANSION	ALLEN BRADLEY FIBER EXPANSION	NUMBER OF DOWNLINK PATCH CORDS	ALLEN BRADLEY UPLINK TRANSCEIVER	NUMBER OF UPLINK PATCH CORDS
Z22N-6DAD5	316 STAINLESS STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SBAB5	4/12 STEEL	(1) 1783-MS10T	NONE	NONE	(8) UTP COPPER	(2) 1783-SFP100FX	(2) OM3 MM FIBER
Z22N-SBBE5S	4/12 STEEL	(1) 1783-MS10T	(1) 1783-MX08T	NONE	(16) STP COPPER	(2) 1783-SFP1GLX	(2) OS2 SM FIBER
Z22N-SDAA5	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	NONE	(2) UTP COPPER
Z22N-SDAB5	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP100FX	(2) OM3 MM FIBER
Z22N-SDAD5	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SEAD5	4/12 STEEL	(1) 1783-BMS20CGP	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SGAA5	4/12 STEEL	(1) 1783-RMS10T	N/A	N/A	(8) UTP COPPER	NONE	(2) UTP COPPER
Z22N-SHAA5	4/12 STEEL	(1) 1783-BMS20CGN	N/A	N/A	(16) UTP COPPER	NONE	(2) UTP COPPER
Z22N-SHAD5	4/12 STEEL	(1) 1783-BMS20CGN	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SIAD5	4/12 STEEL	(1) 1783-BMS10CGN	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z22N-SNA5	4/12 STEEL	(1) 1783-BMS20CL	N/A	N/A	(16) UTP COPPER	NONE	(2) UTP COPPER
Z22N-SRAB5	4/12 STEEL	(1) 1783-BMS20CA	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP100FX	(2) OM3 MM FIBER
Z22N-SD2D5	4/12 STEEL	(2) 1783-BMS10CGA	N/A	N/A	(16) UTP COPPER	(4) 1783-SFP1GSX	(4) OM3 MM FIBER

NOTES:

- CAT 6 UTP COPPER PATCH CORDS AND JACKS, PANDUIT PART NUMBERS (UTP28SP3) AND (CJ688TGIW)
- CAT 6A STP COPPER PATCH CORDS AND JACKS, PANDUIT PART NUMBERS (STP28XIMIG) AND (CJS6X88TGY)
- SM, FIBER PATCH CORDS AND ADAPTERS, PANDUIT PART NUMBERS (F92ERLNLNSNM001) AND (CMDSLCZBU)
- MM, OM3 FIBER PATCH CORDS AND ADAPTERS, PANDUIT PART NUMBER (FX2ERLNLNSNM001) AND (CMDSAQLCZBL)
- SFP TRANSCEIVERS, 1 GIG SINGLE-MODE, ALLEN-BRADLEY PART NUMBER (1783-SFP1GLX)
- SFP TRANSCEIVERS, 100 BASE MULTIMODE, ALLEN-BRADLEY PART NUMBER (1783-SFP100FX)
- SFP TRANSCEIVERS, 1 GIG MULTIMODE, ALLEN-BRADLEY PART NUMBER (1783-SFP1GSX)

					TITLE INTEGRATED NETWORK ZONE SYSTEM, ALLEN-BRADLEY STRATIX 5700, 8000, AND 8300 SWITCHES WITH OPTIONAL EXPANSIONS AND INCLUDED CONNECTIVITY CUSTOMER DRAWING							
					ITEM REVISION NAME 15V510TP/00.PRT							
					DATASET FILE NAME 15V510TP_DC/00A.PRT							
					UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES +/- 0.03 METRIC - MILLIMETER +/- 0.8 X.X +/- 0.018 X.X +/- 0.46 X.XX +/- 0.007 X.XX +/- 0.18 X.XXX +/- 0.007 X.XX +/- 0.18							
					MATERIAL/COLOR: N/A							
					DRAWING NUMBER: 15V510TP							
OOA	3/12/18	JBO	NWW	TIMH	REFER TO SHEET 1	 THIRD ANGLE PROJECTION						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 3 OF 3	SIZE
							JBO	3/12/18	NWW	1:8		A