


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



WIDTH	HEIGHT	DEPTH	WEIGHT
24"	36"	12"	110 LBS / 50 KG

NOTES:

- Each Zone System includes:
 - Allen-Bradley(TM) Stratix(TM) industrial switch with sufficient expansion modules to obtain the specified number of down-link ports.
 - Allen-Bradley(TM) fiber uplinks or copper uplinks.
 - Allen-Bradley(TM) 24 Volt Power Supplies.
 - Panduit 24 Volt UPS (UPS003024024015) and Load Sense Module (UPS003LSM).
 - One dedicated 5ft copper patch cord for UPS remote management.
 - 3ft copper patch cords and CAT6 MINI-COM(R) copper modules to accommodate the number of downlink ports.
 - 48 Port Modular Patch Panel.
 - Either 1 meter Fiber optic uplink patch cords with fiber optic adapter modules, or 3ft copper patch cords with CAT6 MINI-COM(R) copper modules to accommodate the amount of uplinks.
 - Fiber Surface Mount Box for Fiber Optic uplink patching.
 - All Cable Management systems pre-installed (including strain relief bars, L-rings and fiber slack spool), protective cover over all AC wiring and devices, and a gland plate for cabling entry and exit.
- All Network Zone Systems require a 100-250V ac single-phase feed.
- All Network Zone Systems comply with UL 508A standards, and all have UL type 4/12 and IP66 ratings.
- Electrical components rated for use in Class 1, Division 2 environments.
- The Network Zone System is wall mountable with the option to use outside-mount flanges which are included.
- 316 Stainless steel enclosures are rated NEMA 4X.
- Steel and 316 stainless steel enclosures are made from 16 gauge steel.

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
03A	3/3/15	RHG	NWW	TIMH	UPDATED PART NUMBER TABLE	12V304CT


TITLE		Z23N-***A**5*		NETWORK ZONE SYSTEM	
ITEM REVISION NAME		12V304CT/03.PRT		PANDUIT TM	
DATASET FILE NAME		12V304CT_DC/03A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:		N/A	
INCHES	± 0.03	METRIC - MILLIMETER	± 0.8	DRAWING NUMBER:	
X.X	± 0.018	X.X	± 0.46	12V304CT	
X.XX	± 0.007	X.XX	± 0.18	SHT 1 OF 2	
THIRD ANGLE PROJECTION		SCALE		SIZE	
DRAWN BY		DATE		A	
NWW		4-24-14		A	

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	ENCLOSURE TYPE	ALLEN BRADLEY SWITCH	ALLEN BRADLEY COPPER EXPANSION	ALLEN BRADLEY FIBER EXPANSION	NUMBER OF DOWNLINK PATCH CORDS	ALLEN BRADLEY UPLINK TRANSCEIVER	NUMBER OF UPLINK PATCH CORDS
Z23N-6BAAD5	316 STAINLESS STEEL	(1) 1783-MS10T	NONE	NONE	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-6BABD5	316 STAINLESS STEEL	(1) 1783-MS10T	(1) 1783-MX08T	NONE	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SBAAD5	4/12 STEEL	(1) 1783-MS10T	NONE	NONE	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SBABA5	4/12 STEEL	(1) 1783-MS10T	(1) 1783-MX08T	NONE	(16) UTP COPPER	NONE	(2) UTP COPPER
Z23N-SBABD5	4/12 STEEL	(1) 1783-MS10T	(1) 1783-MX08T	NONE	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SBACA5	4/12 STEEL	(1) 1783-MS10T	(2) 1783-MX08T	NONE	(24) UTP COPPER	NONE	(2) UTP COPPER
Z23N-SBACD5	4/12 STEEL	(1) 1783-MS10T	(2) 1783-MX08T	NONE	(24) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SBACF5	4/12 STEEL	(1) 1783-MS10T	(2) 1783-MX08T	NONE	(24) UTP COPPER	(2) 1783-SFP1GSX	(2) OM1 MM W_62.5 FIBER
Z23N-SBAGD5	4/12 STEEL	(1) 1783-MS10T	NONE	(1) 1783-MX08F	(8) UTP COPPER / (8) FIBER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SBA1D5	4/12 STEEL	(1) 1783-MS10T	(1) 1783-MX08T	(1) 1783-MX08F	(16) UTP COPPER / (8) FIBER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SDAAD5	4/12 STEEL	(1) 1783-BMS10CGA	N/A	N/A	(8) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SEAAD5	4/12 STEEL	(1) 1783-BMS20CGP	N/A	N/A	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SGABA5	4/12 STEEL	(1) 1783-RMS10T	(1) 1783-MX08T	NONE	(16) UTP COPPER	NONE	(2) UTP COPPER
Z23N-SGABD5	4/12 STEEL	(1) 1783-RMS10T	(1) 1783-MX08T	NONE	(16) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SGACD5	4/12 STEEL	(1) 1783-RMS10T	(2) 1783-MX08T	NONE	(24) UTP COPPER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SGA1D5	4/12 STEEL	(1) 1783-RMS10T	(1) 1783-MX08T	(1) 1783-MX08F	(16) UTP COPPER / (8) FIBER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER
Z23N-SGA1D5S	4/12 STEEL	(1) 1783-RMS10T	(1) 1783-MX08T	(1) 1783-MX08F	(16) STP COPPER / (8) FIBER	(2) 1783-SFP1GSX	(2) OM3 MM FIBER



03A	3/3/15	RHG	NWW	TIMH	REFER TO SHEET 1 FOR DETAILS	12V304CT
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		Z23N-***A**5* NETWORK ZONE SYSTEM	
ITEM REVISION NAME		12V304CT/03.PRT	
DATASET FILE NAME		12V304CT_DC/03A.PRT	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		MATERIAL/COLOR:	
INCHES	METRIC - MILLIMETER	N/A	
X.X +/- 0.03	X. +/- 0.8		
X.XX +/- 0.018	X.X +/- 0.46		
X.XXX +/- 0.007	X.XX +/- 0.18		
 THIRD ANGLE PROJECTION		DRAWING NUMBER:	
DRAWN BY		12V304CT	
DATE		SHT 2 OF 2	
CHK		A	
SCALE			
NWW			
4-24-14			
TIMH			
1:8			