


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. SYSTEM INCLUDES:

- (1) PULS 240W 24 VOLT DC POWER SUPPLY (CP10.241-S1)
- (1) ROCKWELL 91.2W 24 VOLT DC POWER SUPPLY (1606-XLSDNET4)
- (1) 100 WATT 24 VOLT DC PANDUIT UPS (UPS00100DC)
- (1) PANDUIT LSM (UPS003LSM)
- (2) STAHL 10 AMP LOCKOUT CONTACT BLOCKS (8082/1-1-01)
- (2) WEIDMULLER RED AND WHITE TERMINAL BLOCKS FOR INCOMING POWER (100-240 VAC 50-60HZ)
- (1) PANDUIT 6-PORT GROUND BAR



2. POWER CIRCUIT DESIGNED FOR ONE 24 VOLT DC INDUSTRIAL ETHERNET SWITCHES NOT TO EXCEED 42 WATTS PER SWITCH

3. ALL ACTIVE COMPONENTS RATED FOR USE CLASS 1, DIVISION 2 ENVIRONMENTS

4. ALL ZONE SYSTEMS COMPLY WITH UL 508A STANDARDS

5. ALL ZONE SYSTEMS REQUIRE A 100-240 VOLT AC SINGLE-PHASE FEED

6. INTERNAL WIRING NOT SHOWN, SEE DRAWING (15V510RJ) FOR COMPLETE SCHEMATIC

							TITLE		NETWORK ZONE SYSTEM, 100-240VAC INPUT, REDUNDANT 24VDC POWER SUPPLIES, ONE 24VDC PANDUIT UPS		
							CUSTOMER DRAWING				
							ITEM REVISION NAME		15V510JI/02		
							DATASET FILE NAME		15V510JI_DC/02A		
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]				
							.x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ] .xx ± .01 [ .25 ]      ANGLES ± 5 °				
							THIRD ANGLE PROJECTION		DRAWING NUMBER: 15V510JI		
02A	2/1/18	JBO	NWW	TIMH	RELEASED TO CUSTOMER	ECN-INI-0001/01			SHT 1 OF 1		A
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE
							JBO	10/26/16	NWW	1:4	A

D10100DA/14