PANDUIT® ELECTRICAL SOLUTIONS

A. System Overview

B1. Cable Ties

B2. Cable Accessories

B3. Stainless Steel Ties

> C1. Wiring Duct

C2. Surface Raceway

C3. Abrasion Protection

C4. Cable Management

> D1. Terminals

D2. Power Connectors

D3. Grounding Connectors

E1. Labeling Systems

> E2. Labels

E3. Pre-Printed & Write-On Markers

E4. Permanent Identification

E5. Lockout/ Tagout & Safety Solutions

> F. Index

CT-2500 Battery Powered Crimping Tool

- Quick two-second crimping cycle results in less time to crimp terminals compared to conventional methods
- Lightweight 3.3 lb. design provides maximum productivity and ease of use in continuous workflow operations

• Interchangeable crimp heads for termination of all Panduit #22 – 10 AWG terminals, disconnects, and splices



CT-2500



CT-2550CH



CT-2500BC

| Part Number | Part Description | Std. Pkg. Qty. |
|----------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|
| Crimping Tools | | |
| CT-2500 | Crimps Panduit #22 – 10 AWG insulated and non-insulated terminals, disconnects and splices. Includes tool, two battery cartridges (CT-2500BC), battery charger (CT-2500CHR) and molded carrying case (CT-2500CASE). These parts are also compatible with the CT-2600. Crimp heads not included. Meets U.S. voltage requirements. | 1 |
| CT-2500/E | Crimps Panduit #22 – 10 AWG insulated and non-insulated terminals, disconnects and splices. Includes tool, two battery cartridges (CT-2500CBC), battery charger (CT-2500CHR/E) and molded carrying case (CT-2500CASE). These parts are also compatible with the CT-2600/E. Crimp heads not included. Meets European voltage requirements. | 1 |

Crimp Head Frames

| CT-2550CH | Crimps Panduit #22 – 10 AWG insulated terminals, disconnects, and splices. | 1 |
|-----------|-----------------------------------------------------------------------------------------|---|
| CT-2525CH | Crimps Panduit #22 – 10 AWG fully insulated disconnects and insulated parallel splices. | 1 |
| CT-2570CH | Crimps Panduit #22 – 10 AWG non-insulated terminals, disconnects, and splices. | 1 |

Die Inserts For Use With CT-2500CH Crimp Head Frame

| CD-525 | Die insert used with CT-2500CH (sold separately) to crimp Panduit #22 – 10 AWG fully insulated disconnects and insulated parallel splices. | 1 |
|--------|--------------------------------------------------------------------------------------------------------------------------------------------|---|
| CD-550 | Die insert used with CT-2500CH (sold separately) to crimp Panduit #22 – 10 AWG insulated terminals, disconnects, and splices. | 1 |
| CD-570 | Die insert used with CT-2500CH (sold separately) to crimp Panduit #22 – 10 AWG non-insulated terminals, disconnects, and splices. | 1 |

Accessories

| Addedooned | | |
|--------------|-------------------------------------------------------------------------------|---|
| CT-2500CHR | U.S. compatible battery charger for use with the CT-2500 and the CT-2600. | 1 |
| CT-2500CHR/E | European compatible battery charger for use with the CT-2500/E and CT-2600/E. | 1 |
| CT-2500BC | Rechargeable tool battery for use with the CT-2500 and CT-2600. | 1 |
| CT-2500CASE | Carrying case, holds tool (CT-2500 or CT-2600) and accessories. | 1 |