2										1									
		THIS COP	Y IS	PROV I	DED (ON A RESTRICTED BAS	SIS AND	IS NOT TO BE US	SED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.										
						PANDUIT	MAT'L			DIMENSIONS			I	WEIGHT	USE WITH ANY OF]			
				PART NUMBER*	SUFFIX	MATER	RIAL	'A'	'B'	'C' REF.	'D' REF.	'E' REF.	lbs/100 pcs (g)/100 pcs	THESE CABLE TIE CROSS-SECTIONS					
						CR2	NONE NYLON		N 6/6	0.13		0.33	0.24	0.20	0.04 [18.1]	M, I, S			
						NONE	NYLON									1			
						CR4H	0	WEATHER RESIST (BLA		0.17	0.33 0.57 [8.38] [14.6]	0.57			0.16 [72.6]	M, I, S, LH			
							30	HEAT STABILIZE (BLAC	D NYLON 6/6	[4.32]		[14.6]							
В		L		v C v			1	,	,	· · · · · · · · · · · · · · · · · · ·									
				REF															
			· '	*B * -	-														
	_	++								NOTES:									
		▼								NOTES: 1. SEE www.panduit.com FOR CURRENT									
	_₩					REF 			PART NUMBER SUFFIX DESIGNATION AND FOR PACKAGE SIZE AND PART COLOR.										
		H							2. CABLE TIE CROSS-SECTION CODE:										
✓∟										M=MINATURE. I=INTERMEDIATE.									
7											S=STANDARD, LH=LIGHT HEAVY.								
					т,				3. BAG MAY CONTAIN EXTRA PIECES TO COMPENSATE FOR VARIANCE IN THE										
		H+ 11			1 1					PACKAGING PROCESS. PANDUIT ASSURES MINIMUM PIECE COUNT AS									
						v E v					STATE					20111 713			
		- 			 	REF													
		1+			+1	•				DI	MENSI	ONS	IN E	BRACI	KETS ARE	METRIC [mm]			
										TITLE					ı				
Α											CR2/CR4H - CONNECTOR RING								
									CUSTOMER DRAWING										
										ITEM REVISION	10	B015JM.	/02						
										DATASET FILE		_DC_GB	C_GB0239EB/13			ANDUIT			
										UNL DIMENSI	ESS OTHE	ERWISE LERANC	SPECI ES ARE	FIED, : IN [mm] MATERIAL:				
	13	12/4/2020	RVU	JADE	RMHI	ADDED NOTE 3.			GAECN05827	.× ± 0.	05 [1.3	3]	.xxx ± .(. 1 010	25 1 St	EE TABLE			
JA/20	12	5/08/13	BWG	JADE	RTFI	UPDATED NOTE 1 AND	TITLE BO	ORDER.	GB0239EB/12			_	THIR	D ANGL ECTION	DRAWING NUM	B0239EB			
D10100DA/20	REV	DATE BY CHK APR DESCRIPTION				ECN	DRAWN BY DAT	8/26/96	6 J <i>и</i>	ADE sc	NON	E	SHT 1 0F 1						
	2												1		<u> </u>				